

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211678

Luminaire Tested: **LE_4B20D010 EC4B10209035 4LBM1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B20D010 EC4B10209035 4LBM1LI
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86W DE010-20.46W D5LT-21.24W DMX-20.89W DL2-22.5W
DL3-21.8 6W DLE-22.46W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1909.1 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211678

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBM1LI

Luminous Intensity Polar Plot





TEST NUMBER: P211678

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBM1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211678

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBM1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.5	14.3
10°-20°	609.2	31.9
20°-30°	605.7	31.7
30°-40°	329.8	17.3
40°-50°	76.2	4.0
50°-60°	10.8	0.6
60°-70°	4.0	0.2
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1487.4	77.9
0°-40°	1817.2	95.2
0°-60°	1904.2	99.7
0°-90°	1909.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1909.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3010	
5°	2947	272
15°	2199	609
25°	1328	606
35°	510	330
45°	88	76
55°	12	11
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P211678

CATALOG NUMBER: LE_4B20D010 EC4B10209035 4LBM1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3009.6
2.5°	3002.7
5°	2947.2
7.5°	2834.0
10°	2676.9
12.5°	2446.0
15°	2198.9
17.5°	1954.0
20°	1713.8
22.5°	1517.5
25°	1328.1
27.5°	1147.9
30°	944.7
32.5°	718.3
35°	510.4
37.5°	344.2
40°	224.0
42.5°	140.9
45°	87.8
47.5°	50.8
50°	25.4
52.5°	13.8
55°	11.6
57.5°	7.0
60°	7.0
62.5°	4.6
65°	4.6
67.5°	2.3
70°	2.3
72.5°	2.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)