

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P212120

Luminaire Tested: **LE_4B30D010 EC4B30509040 4LBN1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P212120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LE_4B30D010 EC4B30509040 4LBN1MW
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4W DE010-27.95W D5LT-27.65W DMX-27.73W DL2-29.56W
DL3-29.67W DLE-29.73W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2095.5 lumens
Efficiency: N/A
Efficacy: 74.8 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P212120

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1MW

Luminous Intensity Polar Plot






TEST NUMBER: P212120

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	80	96	89	83	79	86	82	78		84	80	76		81
4	92	83	76	71	90	82	76	71	80	74	70		78	73	69		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62
8	73	62	55	50	71	61	55	50	60	54	50		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	47	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P212120

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.5	7.8
10°-20°	430.3	20.5
20°-30°	566.3	27.0
30°-40°	440.9	21.0
40°-50°	214.1	10.2
50°-60°	135.3	6.5
60°-70°	87.2	4.2
70°-80°	45.6	2.2
80°-90°	11.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1161.1	55.4
0°-40°	1602.0	76.4
0°-60°	1951.4	93.1
0°-90°	2095.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2095.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1788	
5°	1754	164
15°	1535	430
25°	1248	566
35°	706	441
45°	266	214
55°	150	135
65°	86	87
75°	43	46
85°	10	11
90°	0	



TEST NUMBER: P212120

CATALOG NUMBER: LE_4B30D010 EC4B30509040 4LBN1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1787.7
2.5°	1777.7
5°	1754.4
7.5°	1714.5
10°	1661.2
12.5°	1601.3
15°	1534.7
17.5°	1464.7
20°	1391.5
22.5°	1321.6
25°	1248.4
27.5°	1155.1
30°	1028.7
32.5°	878.8
35°	705.7
37.5°	546.0
40°	422.8
42.5°	329.6
45°	266.3
47.5°	216.3
50°	189.8
52.5°	169.8
55°	149.8
57.5°	133.2
60°	116.5
62.5°	99.9
65°	86.5
67.5°	76.6
70°	63.2
72.5°	53.2
75°	43.3
77.5°	33.3
80°	23.3
82.5°	16.6
85°	10.0
87.5°	3.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)