

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210736

Luminaire Tested: **LSR4B10D010BZ EC4B10208027 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210736
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208027 4LBSWH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1014.3 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210736

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P210736

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210736

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.8	5.5
10°-20°	144.4	14.2
20°-30°	188.9	18.6
30°-40°	200.0	19.7
40°-50°	186.5	18.4
50°-60°	141.3	13.9
60°-70°	76.5	7.5
70°-80°	20.6	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.1	38.4
0°-40°	589.1	58.1
0°-60°	916.9	90.4
0°-90°	1014.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1014.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	605	
5°	596	56
15°	516	144
25°	411	189
35°	320	200
45°	243	187
55°	159	141
65°	77	77
75°	18	21
85°	0	0
90°	0	



TEST NUMBER: P210736

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	604.9
2.5°	602.7
5°	596.0
7.5°	581.6
10°	562.7
12.5°	540.5
15°	516.1
17.5°	488.4
20°	464.0
22.5°	436.2
25°	410.7
27.5°	385.1
30°	360.7
32.5°	339.6
35°	319.7
37.5°	299.7
40°	280.8
42.5°	261.9
45°	243.1
47.5°	222.0
50°	200.9
52.5°	179.8
55°	158.7
57.5°	136.5
60°	115.4
62.5°	95.5
65°	76.6
67.5°	58.8
70°	43.3
72.5°	30.0
75°	17.8
77.5°	7.8
80°	2.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)