

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210737

Luminaire Tested: **LSR4B10D010BZ EC4B10208027 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208027 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1022.7 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210737

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P210737

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90						
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79						
3	96	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70						
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62						
5	83	73	65	59	82	72	64	59	70	63	59	68	62	58	66	61	57	56						
6	78	66	59	53	76	65	58	53	64	57	53	62	57	52	61	56	52	50						
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45						
8	68	56	49	44	67	56	48	43	54	48	43	53	47	43	52	47	43	41						
9	64	52	45	40	63	52	45	40	50	44	40	49	44	39	49	43	39	38						
10	60	48	41	37	59	48	41	37	47	41	36	46	40	36	45	40	36	35						

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210737

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.9	5.9
10°-20°	158.8	15.5
20°-30°	213.2	20.8
30°-40°	218.3	21.3
40°-50°	188.9	18.5
50°-60°	125.6	12.3
60°-70°	51.6	5.0
70°-80°	6.1	0.6
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	431.9	42.2
0°-40°	650.2	63.6
0°-60°	964.7	94.3
0°-90°	1022.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1022.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	638	60
15°	567	159
25°	465	213
35°	349	218
45°	246	189
55°	139	126
65°	51	52
75°	3	6
85°	0	0
90°	0	



TEST NUMBER: P210737

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	648.2
2.5°	646.9
5°	638.1
7.5°	624.7
10°	606.6
12.5°	586.5
15°	567.1
17.5°	542.3
20°	518.2
22.5°	492.7
25°	465.2
27.5°	435.7
30°	406.2
32.5°	376.7
35°	348.6
37.5°	321.8
40°	296.3
42.5°	270.8
45°	246.0
47.5°	219.9
50°	193.1
52.5°	166.2
55°	139.4
57.5°	116.0
60°	91.8
62.5°	69.7
65°	50.9
67.5°	33.5
70°	19.4
72.5°	9.4
75°	2.7
77.5°	1.3
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)