

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210753

Luminaire Tested: **LSR4B10D010BZ EC4B10209027 4LBNB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210753
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35208)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209027 4LBNB1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 341.9 lumens
Efficiency: N/A
Efficacy: 35.1 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.79
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 9.73
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210753

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBNB1

Luminous Intensity Polar Plot





TEST NUMBER: P210753

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBNB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	111	109	107		111	109	107	105		105	103	102			101	100	99			98
2	109	104	100	97		106	102	99	96		99	96	94			96	94	92			93
3	104	98	93	89		102	96	92	88		94	90	87			91	88	86			89
4	99	92	86	82		97	90	86	82		88	84	81			86	83	80			85
5	94	86	81	77		92	85	80	76		84	79	76			82	78	75			80
6	90	81	76	72		88	81	75	71		79	74	71			78	74	70			76
7	86	77	71	67		84	76	71	67		75	70	67			74	69	66			73
8	82	73	67	63		80	72	67	63		71	66	63			70	66	62			69
9	78	69	63	60		77	68	63	59		67	63	59			67	62	59			66
10	75	65	60	56		74	65	60	56		64	59	56			63	59	56			63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61077
5°	56813
10°	47818
15°	39703
20°	34300
25°	30501
30°	24980
35°	15339
40°	6133
45°	1391
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P210753

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBNB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.6	13.6
10°-20°	98.8	28.9
20°-30°	114.6	33.5
30°-40°	71.8	21.0
40°-50°	10.1	3.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	260.0	76.0
0°-40°	331.8	97.0
0°-60°	341.9	100.0
0°-90°	341.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	341.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	559	
5°	518	47
15°	351	99
25°	253	115
35°	115	72
45°	9	10
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P210753

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBNB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	559
2.5°	548
5°	518
7.5°	475
10°	431
12.5°	389
15°	351
17.5°	319
20°	295
22.5°	273
25°	253
27.5°	229
30°	198
32.5°	159
35°	115
37.5°	75
40°	43
42.5°	22
45°	9
47.5°	2
50°	0
52.5°	0
55°	0
57.5°	0
60°	0
62.5°	0
65°	0
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)