

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210743

Luminaire Tested: **LSR4B10D010BZ EC4B10208027 4LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210743
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208027 4LBWWH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 891.3 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210743

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBWWH1

Luminous Intensity Polar Plot




TEST NUMBER: P210743
CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		0			
RCR																						
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102	100
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94	92
2	106	101	96	92		104	99	95	91		96	92	89		93	90	87		90	87	85	84
3	100	93	87	82		98	91	86	82		88	84	80		86	82	79		84	80	78	76
4	94	85	79	74		92	84	78	74		82	77	73		80	75	72		78	74	71	69
5	88	79	72	67		86	78	71	67		76	70	66		74	69	65		72	68	65	63
6	83	73	66	61		81	72	65	61		70	64	60		69	64	60		67	63	59	58
7	78	67	60	56		76	67	60	55		65	59	55		64	59	55		63	58	54	53
8	73	62	56	51		72	62	55	51		61	55	51		60	54	50		59	54	50	49
9	69	58	51	47		68	58	51	47		57	51	47		56	50	47		55	50	46	45
10	65	54	48	43		64	54	48	43		53	47	43		52	47	43		51	46	43	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210743

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.0	6.1
10°-20°	167.0	18.7
20°-30°	256.9	28.8
30°-40°	247.9	27.8
40°-50°	129.2	14.5
50°-60°	27.2	3.1
60°-70°	6.3	0.7
70°-80°	2.5	0.3
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.9	53.6
0°-40°	725.8	81.4
0°-60°	882.3	99.0
0°-90°	891.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	891.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	557	
5°	562	54
15°	591	167
25°	563	257
35°	402	248
45°	164	129
55°	24	27
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P210743

CATALOG NUMBER: LSR4B10D010BZ EC4B10208027 4LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	557.2
2.5°	558.4
5°	561.9
7.5°	566.6
10°	573.6
12.5°	582.9
15°	591.0
17.5°	595.7
20°	592.2
22.5°	585.2
25°	563.1
27.5°	536.2
30°	501.3
32.5°	454.6
35°	402.2
37.5°	345.1
40°	285.6
42.5°	226.2
45°	164.4
47.5°	110.7
50°	71.1
52.5°	43.1
55°	24.5
57.5°	15.2
60°	10.5
62.5°	8.2
65°	5.8
67.5°	4.7
70°	3.5
72.5°	3.5
75°	2.3
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)