

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210761

Luminaire Tested: **LSR4B10D010BZ EC4B10209027 4LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210761
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209027 4LBSGPH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 794.4 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210761

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBSGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P210761

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	102	99		101	98	96		97	95	93		93	91	90
2	102	95	89	84		100	93	88	83		90	85	82		87	83	80		84	81	78
3	94	85	78	72		92	83	77	71		80	75	70		78	73	69		75	71	68
4	87	76	68	62		85	75	67	62		72	66	61		70	65	60		68	63	59
5	80	68	60	54		78	67	60	54		65	59	53		63	58	53		62	56	52
6	74	62	54	48		73	61	53	48		59	52	47		58	52	47		56	51	47
7	69	57	48	43		68	56	48	43		54	47	42		53	47	42		52	46	42
8	65	52	44	38		63	51	44	38		50	43	38		49	42	38		48	42	38
9	60	48	40	35		59	47	40	35		46	39	35		45	39	34		44	38	34
10	57	44	37	32		56	44	36	32		43	36	31		42	36	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210761

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.7	4.4
10°-20°	97.5	12.3
20°-30°	142.2	17.9
30°-40°	162.2	20.4
40°-50°	155.6	19.6
50°-60°	119.2	15.0
60°-70°	65.4	8.2
70°-80°	17.4	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	274.5	34.6
0°-40°	436.7	55.0
0°-60°	711.4	89.5
0°-90°	794.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	794.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	369	
5°	366	35
15°	346	98
25°	309	142
35°	259	162
45°	202	156
55°	134	119
65°	66	65
75°	15	17
85°	0	0
90°	0	



TEST NUMBER: P210761

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	369.0
2.5°	368.0
5°	366.1
7.5°	363.3
10°	359.4
12.5°	352.8
15°	346.1
17.5°	338.5
20°	329.9
22.5°	319.4
25°	308.9
27.5°	298.4
30°	285.1
32.5°	272.7
35°	259.3
37.5°	246.0
40°	232.6
42.5°	218.3
45°	202.1
47.5°	185.9
50°	168.8
52.5°	150.6
55°	133.5
57.5°	116.3
60°	98.2
62.5°	81.0
65°	65.8
67.5°	50.5
70°	37.2
72.5°	24.8
75°	15.3
77.5°	6.7
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)