

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210756

Luminaire Tested: **LSR4B10D010BZ EC4B10209027 4LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35291)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209027 4LBNLI1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 649.3 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 9.73
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210756

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBNI1

Luminous Intensity Polar Plot





TEST NUMBER: P210756

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			95
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			90
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			85
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			81
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			77
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			73
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			69
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			66
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			63
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	182575
5°	164298
10°	127366
15°	92189
20°	63834
25°	46535
30°	33812
35°	20007
40°	8415
45°	2627
50°	340
55°	190
60°	219
65°	259
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P210756

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.7	20.3
10°-20°	225.4	34.7
20°-30°	179.2	27.6
30°-40°	94.8	14.6
40°-50°	16.3	2.5
50°-60°	1.2	0.2
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.3	82.6
0°-40°	631.1	97.2
0°-60°	648.7	99.9
0°-90°	649.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	649.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1671	
5°	1498	132
15°	815	225
25°	386	179
35°	150	95
45°	17	16
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P210756

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1671
2.5°	1628
5°	1498
7.5°	1328
10°	1148
12.5°	974
15°	815
17.5°	667
20°	549
22.5°	459
25°	386
27.5°	327
30°	268
32.5°	208
35°	150
37.5°	99
40°	59
42.5°	34
45°	17
47.5°	6
50°	2
52.5°	2
55°	1
57.5°	1
60°	1
62.5°	1
65°	1
67.5°	0
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)