

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210765

Luminaire Tested: **LSR4B10D010BZ EC4B10209027 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210765
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209027 4LBSWH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 870.5 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210765

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P210765

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210765

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	5.5
10°-20°	124.0	14.2
20°-30°	162.1	18.6
30°-40°	171.7	19.7
40°-50°	160.1	18.4
50°-60°	121.3	13.9
60°-70°	65.7	7.5
70°-80°	17.6	2.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.0	38.4
0°-40°	505.6	58.1
0°-60°	787.0	90.4
0°-90°	870.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	870.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	519	
5°	512	48
15°	443	124
25°	352	162
35°	274	172
45°	209	160
55°	136	121
65°	66	66
75°	15	18
85°	0	0
90°	0	



TEST NUMBER: P210765

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	519.2
2.5°	517.3
5°	511.6
7.5°	499.2
10°	483.0
12.5°	464.0
15°	443.0
17.5°	419.2
20°	398.2
22.5°	374.4
25°	352.5
27.5°	330.6
30°	309.6
32.5°	291.5
35°	274.4
37.5°	257.2
40°	241.0
42.5°	224.8
45°	208.6
47.5°	190.5
50°	172.4
52.5°	154.3
55°	136.2
57.5°	117.2
60°	99.1
62.5°	81.9
65°	65.7
67.5°	50.5
70°	37.2
72.5°	25.7
75°	15.2
77.5°	6.7
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)