

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210771

Luminaire Tested: **LSR4B10D010BZ EC4B10209027 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35172)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209027 4LBWMW1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 770.7 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 9.73
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210771

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P210771

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		93	92	90
2	103	96	91	86		101	94	89	85		91	87	83		88	84	81		85	82	80
3	96	87	80	75		93	85	79	74		83	77	73		80	76	72		78	74	71
4	89	79	72	66		87	78	71	66		75	69	65		73	68	64		71	67	63
5	83	72	64	59		81	71	64	58		69	63	58		67	62	57		65	61	57
6	78	66	58	53		76	65	58	53		64	57	52		62	56	52		60	55	51
7	73	61	53	48		71	60	53	48		59	52	47		57	51	47		56	51	47
8	68	56	49	44		67	56	49	44		54	48	43		53	47	43		52	47	43
9	64	52	45	40		63	52	45	40		51	44	40		50	44	40		49	43	39
10	61	49	42	37		59	48	41	37		47	41	37		46	41	37		46	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	51025
5°	50781
10°	50148
15°	49205
20°	47788
25°	45811
30°	42139
35°	36013
40°	29096
45°	22405
50°	17508
55°	14668
60°	13330
65°	12151
70°	11181
75°	10132
80°	8809
85°	7522



TEST NUMBER: P210771

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.8	5.7
10°-20°	122.6	15.9
20°-30°	173.3	22.5
30°-40°	167.9	21.8
40°-50°	113.3	14.7
50°-60°	70.3	9.1
60°-70°	47.0	6.1
70°-80°	25.7	3.3
80°-90°	6.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	339.8	44.1
0°-40°	507.6	65.9
0°-60°	691.2	89.7
0°-90°	770.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	770.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	467	
5°	463	44
15°	435	123
25°	380	173
35°	270	168
45°	145	113
55°	77	70
65°	47	47
75°	24	26
85°	6	7
90°	0	



TEST NUMBER: P210771

CATALOG NUMBER: LSR4B10D010BZ EC4B10209027 4LBWMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	467
2.5°	467
5°	463
7.5°	458
10°	452
12.5°	446
15°	435
17.5°	426
20°	411
22.5°	396
25°	380
27.5°	358
30°	334
32.5°	303
35°	270
37.5°	237
40°	204
42.5°	171
45°	145
47.5°	121
50°	103
52.5°	88
55°	77
57.5°	68
60°	61
62.5°	54
65°	47
67.5°	41
70°	35
72.5°	30
75°	24
77.5°	19
80°	14
82.5°	10
85°	6
87.5°	2
90°	0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)