

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210775

Luminaire Tested: **LSR4B10D010BZ EC4B10209727 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209727 4LBSCMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 800.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210775

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBSCMW1

Luminous Intensity Polar Plot





TEST NUMBER: P210775

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	110	106	102	99	108	104	100	97	100	97	94		96	93	91		92
2	101	94	87	82	99	92	86	81	88	84	79		85	81	78		82
3	93	83	75	70	90	81	74	69	79	73	68		76	71	67		73
4	85	74	66	60	83	73	65	59	70	64	58		68	62	58		66
5	79	66	58	52	77	65	57	51	63	56	51		61	55	50		60
6	73	60	52	45	71	59	51	45	57	50	45		56	49	44		54
7	68	55	46	40	66	54	46	40	52	45	40		51	44	40		50
8	63	50	42	36	61	49	41	36	48	41	36		47	40	36		46
9	59	46	38	33	57	45	38	32	44	37	32		43	37	32		42
10	55	42	35	30	54	42	34	30	41	34	29		40	34	29		39

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210775

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBSCMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.0	3.9
10°-20°	88.1	11.0
20°-30°	132.6	16.6
30°-40°	157.1	19.6
40°-50°	156.4	19.5
50°-60°	126.0	15.8
60°-70°	76.3	9.5
70°-80°	28.3	3.5
80°-90°	4.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	251.7	31.5
0°-40°	408.8	51.1
0°-60°	691.2	86.4
0°-90°	800.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	800.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	327	
5°	325	31
15°	312	88
25°	288	133
35°	252	157
45°	204	156
55°	141	126
65°	77	76
75°	26	28
85°	3	4
90°	0	



TEST NUMBER: P210775

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	326.8
2.5°	326.8
5°	325.3
7.5°	324.3
10°	321.4
12.5°	316.6
15°	312.2
17.5°	307.4
20°	301.6
22.5°	295.7
25°	288.0
27.5°	279.7
30°	270.5
32.5°	261.8
35°	251.6
37.5°	240.9
40°	228.3
42.5°	216.2
45°	203.6
47.5°	189.6
50°	174.0
52.5°	158.0
55°	140.6
57.5°	125.1
60°	107.6
62.5°	92.1
65°	76.6
67.5°	62.1
70°	48.5
72.5°	36.4
75°	25.7
77.5°	16.5
80°	9.7
82.5°	5.8
85°	3.4
87.5°	1.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)