

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210777

Luminaire Tested: **LSR4B10D010BZ EC4B10209727 4LBMGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209727 4LBMGPH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 414.0 lumens
Efficiency: N/A
Efficacy: 41.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.92
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210777

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBMGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P210777

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBMGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93		
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	88	86		
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79		
4	96	88	82	78	94	87	82	78	85	80	77	83	79	76	81	78	75	73		
5	91	82	76	72	89	81	76	71	79	74	71	78	73	70	76	72	69	68		
6	86	77	71	66	85	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	73	63	57	53	72	63	57	53	62	57	53	61	56	53	60	56	52	51		
10	70	60	54	50	69	59	54	50	59	53	50	58	53	49	57	52	49	48		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210777

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBMGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	9.5
10°-20°	102.1	24.7
20°-30°	131.0	31.6
30°-40°	94.7	22.9
40°-50°	33.9	8.2
50°-60°	9.2	2.2
60°-70°	3.0	0.7
70°-80°	0.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.3	65.8
0°-40°	366.9	88.6
0°-60°	410.0	99.1
0°-90°	414.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	414.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	426	
5°	418	39
15°	364	102
25°	289	131
35°	151	95
45°	41	34
55°	10	9
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210777

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBMGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	425.6
2.5°	423.8
5°	417.7
7.5°	408.2
10°	395.1
12.5°	380.3
15°	363.8
17.5°	347.2
20°	330.7
22.5°	311.6
25°	288.9
27.5°	262.8
30°	229.8
32.5°	191.5
35°	151.4
37.5°	114.9
40°	83.5
42.5°	59.2
45°	40.9
47.5°	27.8
50°	18.3
52.5°	13.1
55°	9.6
57.5°	7.0
60°	5.2
62.5°	4.4
65°	2.6
67.5°	1.7
70°	1.7
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)