

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210784

Luminaire Tested: **LSR4B10D010BZ EC4B10209727 4LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209727 4LBNH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 479.1 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210784

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBNH1

Luminous Intensity Polar Plot






TEST NUMBER: P210784

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210784

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.3	11.3
10°-20°	131.7	27.5
20°-30°	152.9	31.9
30°-40°	101.2	21.1
40°-50°	28.4	5.9
50°-60°	7.1	1.5
60°-70°	2.7	0.6
70°-80°	0.9	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	338.8	70.7
0°-40°	440.0	91.8
0°-60°	475.5	99.2
0°-90°	479.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	602	
5°	586	54
15°	471	132
25°	335	153
35°	162	101
45°	33	28
55°	8	7
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P210784

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	601.6
2.5°	599.0
5°	586.0
7.5°	563.4
10°	535.6
12.5°	504.4
15°	471.4
17.5°	439.3
20°	403.7
22.5°	370.7
25°	335.1
27.5°	301.2
30°	257.8
32.5°	211.8
35°	162.3
37.5°	116.3
40°	79.0
42.5°	51.2
45°	33.0
47.5°	20.0
50°	13.0
52.5°	9.5
55°	7.8
57.5°	6.1
60°	4.3
62.5°	3.5
65°	2.6
67.5°	1.7
70°	1.7
72.5°	0.9
75°	0.9
77.5°	0.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)