

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210795

Luminaire Tested: **LSR4B10D010BZ EC4B10209727 4LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210795
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209727 4LBSWMH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 763.4 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210795

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBSWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P210795

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86
3	96	88	82	76	94	87	81	76	84	79	74		81	77	73		79
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72
5	83	73	65	59	82	72	64	59	70	63	59		68	62	58		66
6	78	66	59	53	76	65	58	53	64	57	53		62	57	52		61
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56
8	68	56	49	44	67	56	48	43	54	48	43		53	47	43		52
9	64	52	45	40	63	52	45	40	50	44	40		49	44	39		49
10	60	48	41	37	59	48	41	37	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210795

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.7	5.9
10°-20°	118.5	15.5
20°-30°	159.2	20.8
30°-40°	162.9	21.3
40°-50°	141.0	18.5
50°-60°	93.8	12.3
60°-70°	38.5	5.0
70°-80°	4.6	0.6
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	322.4	42.2
0°-40°	485.3	63.6
0°-60°	720.1	94.3
0°-90°	763.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	763.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	484	
5°	476	45
15°	423	119
25°	347	159
35°	260	163
45°	184	141
55°	104	94
65°	38	39
75°	2	5
85°	0	0
90°	0	



TEST NUMBER: P210795

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	483.9
2.5°	482.9
5°	476.4
7.5°	466.3
10°	452.8
12.5°	437.8
15°	423.3
17.5°	404.8
20°	386.8
22.5°	367.8
25°	347.3
27.5°	325.2
30°	303.2
32.5°	281.2
35°	260.2
37.5°	240.2
40°	221.2
42.5°	202.2
45°	183.6
47.5°	164.1
50°	144.1
52.5°	124.1
55°	104.1
57.5°	86.6
60°	68.6
62.5°	52.0
65°	38.0
67.5°	25.0
70°	14.5
72.5°	7.0
75°	2.0
77.5°	1.0
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)