

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210800

Luminaire Tested: **LSR4B10D010BZ EC4B10209727 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209727 4LBWMW1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 669.6 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210800

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBWMW1

Luminous Intensity Polar Plot






TEST NUMBER: P210800

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88						
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78						
3	96	87	80	75	93	85	79	74	83	77	73	80	76	72	78	74	71	69						
4	89	79	72	66	87	78	71	66	75	69	65	73	68	64	71	67	63	61						
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55						
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	60	55	51	50						
7	73	61	53	48	71	60	53	48	59	52	47	57	51	47	56	51	47	45						
8	68	56	49	44	67	56	49	44	54	48	43	53	47	43	52	47	43	41						
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38						
10	61	49	42	37	59	48	41	37	47	41	37	46	41	37	46	40	36	35						

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210800

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.1	5.7
10°-20°	106.5	15.9
20°-30°	150.6	22.5
30°-40°	145.9	21.8
40°-50°	98.4	14.7
50°-60°	61.1	9.1
60°-70°	40.8	6.1
70°-80°	22.4	3.3
80°-90°	5.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	295.2	44.1
0°-40°	441.1	65.9
0°-60°	600.6	89.7
0°-90°	669.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	669.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	406	
5°	402	38
15°	378	107
25°	330	151
35°	235	146
45°	126	98
55°	67	61
65°	41	41
75°	21	22
85°	5	6
90°	0	



TEST NUMBER: P210800

CATALOG NUMBER: LSR4B10D010BZ EC4B10209727 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	405.8
2.5°	405.8
5°	402.3
7.5°	398.0
10°	392.7
12.5°	387.5
15°	378.0
17.5°	370.2
20°	357.1
22.5°	344.1
25°	330.2
27.5°	311.1
30°	290.2
32.5°	263.3
35°	234.6
37.5°	205.9
40°	177.3
42.5°	148.6
45°	126.0
47.5°	105.1
50°	89.5
52.5°	76.5
55°	66.9
57.5°	59.1
60°	53.0
62.5°	46.9
65°	40.8
67.5°	35.6
70°	30.4
72.5°	26.1
75°	20.9
77.5°	16.5
80°	12.2
82.5°	8.7
85°	5.2
87.5°	1.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)