

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210960

Luminaire Tested: **LSR4B10D010BZ EC4B10208040 4LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210960
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208040 4LBNMW1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 793.6 lumens
Efficiency: N/A
Efficacy: 80.2 lumens/watt
Spacing Criteria (0/90/45): 0.96 / 0.96 / 0.95
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210960

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBNMW1

Luminous Intensity Polar Plot






TEST NUMBER: P210960

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	80	96	89	83	79	86	82	78		84	80	76		81
4	92	83	76	71	90	82	76	71	80	74	70		78	73	69		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62
8	73	62	55	50	71	61	55	50	60	54	50		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	43	64	54	47	43	53	47	43		52	47	43		51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210960

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.3	7.8
10°-20°	163.0	20.5
20°-30°	214.5	27.0
30°-40°	166.9	21.0
40°-50°	81.1	10.2
50°-60°	51.2	6.5
60°-70°	33.0	4.2
70°-80°	17.3	2.2
80°-90°	4.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	439.7	55.4
0°-40°	606.6	76.4
0°-60°	738.9	93.1
0°-90°	793.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	677	
5°	664	62
15°	581	163
25°	473	214
35°	267	167
45°	101	81
55°	57	51
65°	33	33
75°	16	17
85°	4	4
90°	0	



TEST NUMBER: P210960

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	677.0
2.5°	673.2
5°	664.4
7.5°	649.2
10°	629.1
12.5°	606.4
15°	581.2
17.5°	554.7
20°	527.0
22.5°	500.5
25°	472.7
27.5°	437.4
30°	389.5
32.5°	332.8
35°	267.3
37.5°	206.7
40°	160.1
42.5°	124.8
45°	100.9
47.5°	81.9
50°	71.9
52.5°	64.3
55°	56.7
57.5°	50.4
60°	44.1
62.5°	37.8
65°	32.8
67.5°	29.0
70°	24.0
72.5°	20.2
75°	16.4
77.5°	12.6
80°	8.8
82.5°	6.3
85°	3.8
87.5°	1.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)