

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210961

Luminaire Tested: **LSR4B10D010BZ EC4B10208040 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208040 4LBNWH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 730.5 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210961

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBNWH1

Luminous Intensity Polar Plot






TEST NUMBER: P210961

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	111	109	107	112	109	107	105		105	104	102			102	100	99			95
2	109	105	101	98	107	103	100	97		100	97	95			97	95	93			89
3	104	98	94	90	102	97	93	90		94	91	88			92	89	87			84
4	100	93	88	84	98	92	87	83		90	86	82			88	84	82			79
5	95	88	82	78	94	87	82	78		85	81	77			83	80	77			75
6	91	83	78	74	90	82	77	74		81	76	73			79	76	73			71
7	87	79	73	70	86	78	73	69		77	72	69			76	72	69			67
8	84	75	70	66	82	74	69	66		73	69	65			72	68	65			64
9	80	71	66	62	79	71	66	62		70	65	62			69	65	62			61
10	77	68	63	59	76	68	63	59		67	62	59			66	62	59			58

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210961

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.9	17.4
10°-20°	238.1	32.6
20°-30°	213.7	29.2
30°-40°	122.6	16.8
40°-50°	24.5	3.4
50°-60°	3.1	0.4
60°-70°	1.4	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	578.8	79.2
0°-40°	701.4	96.0
0°-60°	728.9	99.8
0°-90°	730.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	730.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1552	
5°	1428	127
15°	855	238
25°	462	214
35°	194	123
45°	26	24
55°	4	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P210961

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1552.4
2.5°	1520.9
5°	1427.6
7.5°	1291.4
10°	1142.6
12.5°	996.3
15°	855.0
17.5°	731.5
20°	625.5
22.5°	537.2
25°	461.6
27.5°	401.0
30°	334.2
32.5°	266.1
35°	194.2
37.5°	132.4
40°	82.0
42.5°	49.2
45°	26.5
47.5°	11.4
50°	5.0
52.5°	3.8
55°	3.8
57.5°	2.5
60°	2.5
62.5°	1.3
65°	1.3
67.5°	1.3
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)