

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210965

Luminaire Tested: **LSR4B10D010BZ EC4B10208040 4LBSH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208040 4LBSH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1092.4 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210965

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBSH1

Luminous Intensity Polar Plot





TEST NUMBER: P210965

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBSH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		93	92	90
2	102	96	90	85		100	94	88	84		90	86	82		87	83	80		84	81	79
3	95	85	78	73		92	84	77	72		81	75	71		78	74	70		76	72	69
4	87	77	69	63		85	75	68	63		73	67	62		71	65	61		69	64	60
5	81	69	61	55		79	68	61	55		66	60	55		64	59	54		63	58	53
6	75	63	55	49		73	62	54	49		60	54	49		59	53	48		57	52	48
7	70	58	50	44		68	57	49	44		55	49	44		54	48	43		53	47	43
8	65	53	45	40		64	52	45	40		51	44	39		50	44	39		49	43	39
9	61	49	41	36		60	48	41	36		47	40	36		46	40	36		45	40	35
10	58	45	38	33		56	45	38	33		44	37	33		43	37	33		42	37	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210965

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBSH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.5	4.9
10°-20°	145.5	13.3
20°-30°	202.0	18.5
30°-40°	220.4	20.2
40°-50°	205.6	18.8
50°-60°	156.1	14.3
60°-70°	85.5	7.8
70°-80°	23.5	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	401.0	36.7
0°-40°	621.4	56.9
0°-60°	983.1	90.0
0°-90°	1092.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1092.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	566	54
15°	518	145
25°	439	202
35°	352	220
45°	267	206
55°	174	156
65°	85	85
75°	20	23
85°	0	0
90°	0	



TEST NUMBER: P210965

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBSH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	571.3
2.5°	571.3
5°	566.5
7.5°	559.3
10°	548.5
12.5°	534.0
15°	518.4
17.5°	499.2
20°	481.1
22.5°	459.5
25°	439.0
27.5°	418.6
30°	395.7
32.5°	374.1
35°	352.4
37.5°	330.8
40°	310.3
42.5°	288.7
45°	267.0
47.5°	245.4
50°	221.3
52.5°	198.5
55°	174.4
57.5°	151.6
60°	128.7
62.5°	105.8
65°	85.4
67.5°	66.2
70°	49.3
72.5°	33.7
75°	20.4
77.5°	9.6
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)