

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210962

Luminaire Tested: **LSR4B10D010BZ EC4B10208040 4LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208040 4LBPSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1185.9 lumens
Efficiency: N/A
Efficacy: 119.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210962

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P210962

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	110	106	102	99		107	104	100	97		99	97	94		96	93	91		92	90	88
2	101	93	87	82		98	92	86	81		88	83	79		85	81	77		82	79	76
3	93	83	75	69		90	81	74	69		78	72	67		76	70	66		73	69	65
4	85	74	66	59		83	72	65	59		70	63	58		68	62	57		66	61	56
5	78	66	58	51		76	65	57	51		63	56	51		61	55	50		59	54	49
6	73	60	51	45		71	59	51	45		57	50	44		55	49	44		54	48	44
7	67	54	46	40		66	54	46	40		52	45	40		51	44	39		49	43	39
8	63	50	41	36		61	49	41	36		48	41	35		46	40	35		45	39	35
9	59	46	38	32		57	45	37	32		44	37	32		43	36	32		42	36	32
10	55	42	34	29		54	42	34	29		41	34	29		40	33	29		39	33	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210962

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.3	3.8
10°-20°	129.1	10.9
20°-30°	194.4	16.4
30°-40°	231.3	19.5
40°-50°	230.8	19.5
50°-60°	187.7	15.8
60°-70°	115.5	9.7
70°-80°	44.8	3.8
80°-90°	7.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	368.7	31.1
0°-40°	599.9	50.6
0°-60°	1018.5	85.9
0°-90°	1185.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1185.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	478	
5°	476	45
15°	458	129
25°	423	194
35°	370	231
45°	300	231
55°	210	188
65°	116	115
75°	41	45
85°	6	7
90°	0	



TEST NUMBER: P210962

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	477.8
2.5°	478.5
5°	476.4
7.5°	473.6
10°	470.1
12.5°	463.8
15°	458.1
17.5°	449.7
20°	440.6
22.5°	432.1
25°	423.0
27.5°	410.4
30°	397.7
32.5°	385.8
35°	370.3
37.5°	353.4
40°	338.0
42.5°	319.0
45°	300.0
47.5°	279.7
50°	257.9
52.5°	235.4
55°	210.1
57.5°	185.5
60°	161.6
62.5°	138.4
65°	115.9
67.5°	94.9
70°	75.2
72.5°	56.9
75°	40.8
77.5°	26.7
80°	16.2
82.5°	9.8
85°	5.6
87.5°	2.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)