

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210963

Luminaire Tested: **LSR4B10D010BZ EC4B10208040 4LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10208040 4LBSB1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 960.2 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210963

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBSB1

Luminous Intensity Polar Plot






TEST NUMBER: P210963

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210963

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.0	4.2
10°-20°	113.4	11.8
20°-30°	168.7	17.6
30°-40°	196.4	20.4
40°-50°	191.4	19.9
50°-60°	147.2	15.3
60°-70°	81.4	8.5
70°-80°	21.5	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	322.2	33.6
0°-40°	518.5	54.0
0°-60°	857.1	89.3
0°-90°	960.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	960.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	424	
5°	421	40
15°	402	113
25°	366	169
35°	315	196
45°	248	191
55°	164	147
65°	82	81
75°	18	22
85°	0	0
90°	0	



TEST NUMBER: P210963

CATALOG NUMBER: LSR4B10D010BZ EC4B10208040 4LBSB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	423.6
2.5°	423.6
5°	421.1
7.5°	417.5
10°	415.1
12.5°	407.8
15°	401.7
17.5°	395.6
20°	387.1
22.5°	378.5
25°	366.4
27.5°	354.2
30°	342.0
32.5°	328.6
35°	315.3
37.5°	298.2
40°	283.6
42.5°	267.8
45°	248.3
47.5°	230.0
50°	209.4
52.5°	187.4
55°	164.3
57.5°	142.4
60°	121.7
62.5°	101.0
65°	81.6
67.5°	63.3
70°	46.3
72.5°	31.6
75°	18.3
77.5°	8.5
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)