

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210977

Luminaire Tested: **LSR4B10D010BZ EC4B10209040 4LBCSMMS1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210977
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209040 4LBSCMMS1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 821.3 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210977

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBCSMMS1

Luminous Intensity Polar Plot





TEST NUMBER: P210977

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBCSMMS1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	101	98		100	98	95		97	94	92		93	91	90
2	102	95	89	84		99	93	88	83		90	85	81		86	83	79		83	80	78
3	94	85	77	72		92	83	76	71		80	74	70		77	73	69		75	71	67
4	87	76	68	62		84	74	67	61		72	66	61		70	64	60		68	63	59
5	80	68	60	54		78	67	59	54		65	58	53		63	57	53		61	56	52
6	74	62	54	48		72	61	53	47		59	52	47		58	51	47		56	51	46
7	69	56	48	42		67	56	48	42		54	47	42		53	46	42		51	46	41
8	64	52	44	38		63	51	43	38		50	43	38		48	42	38		47	42	37
9	60	48	40	35		59	47	40	34		46	39	34		45	39	34		44	38	34
10	57	44	36	31		55	43	36	31		43	36	31		42	35	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210977

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBCSMMS1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.5	4.3
10°-20°	99.7	12.1
20°-30°	145.7	17.7
30°-40°	166.6	20.3
40°-50°	160.1	19.5
50°-60°	123.6	15.1
60°-70°	69.0	8.4
70°-80°	20.1	2.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	280.9	34.2
0°-40°	447.6	54.5
0°-60°	731.3	89.0
0°-90°	821.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	821.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	377	
5°	374	36
15°	354	100
25°	317	146
35°	267	167
45°	209	160
55°	139	124
65°	69	69
75°	18	20
85°	0	1
90°	0	



TEST NUMBER: P210977

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBCSMMS1

CANDELA DISTRIBUTION (FULL):

	0°
0°	377.1
2.5°	377.1
5°	374.0
7.5°	372.4
10°	367.0
12.5°	360.7
15°	353.8
17.5°	346.9
20°	336.8
22.5°	328.8
25°	316.6
27.5°	304.4
30°	292.1
32.5°	279.9
35°	266.7
37.5°	253.4
40°	238.0
42.5°	224.2
45°	208.8
47.5°	191.2
50°	174.8
52.5°	156.7
55°	138.6
57.5°	120.0
60°	102.5
62.5°	85.0
65°	69.1
67.5°	54.2
70°	40.4
72.5°	28.2
75°	17.5
77.5°	9.0
80°	3.2
82.5°	1.1
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)