

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211000

Luminaire Tested: **LSR4B10D010BZ EC4B10209040 4LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211000
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209040 4LBWGPH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 609.6 lumens
Efficiency: N/A
Efficacy: 61.6 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211000

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBWGP1

Luminous Intensity Polar Plot





TEST NUMBER: P211000

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	99		100	98	96		96	95	94
2	106	100	96	92		104	99	95	91		95	92	89		92	90	87		90	87	85
3	100	92	87	82		98	91	86	81		88	84	80		86	82	79		83	80	77
4	94	85	78	74		92	84	78	73		81	76	72		79	75	71		77	74	71
5	88	78	72	67		86	77	71	66		75	70	66		74	69	65		72	68	64
6	83	72	65	61		81	71	65	60		70	64	60		68	63	59		67	63	59
7	78	67	60	55		76	66	60	55		65	59	55		64	58	55		63	58	54
8	73	62	56	51		72	62	55	51		61	55	51		59	54	50		58	54	50
9	69	58	51	47		68	58	51	47		57	51	47		56	50	46		55	50	46
10	65	54	48	43		64	54	48	43		53	47	43		52	47	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211000

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.4	6.8
10°-20°	117.3	19.2
20°-30°	168.2	27.6
30°-40°	158.4	26.0
40°-50°	87.5	14.3
50°-60°	28.0	4.6
60°-70°	7.0	1.1
70°-80°	1.7	0.3
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.9	53.6
0°-40°	485.3	79.6
0°-60°	600.8	98.5
0°-90°	609.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	609.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	439	
5°	437	41
15°	416	117
25°	369	168
35°	257	158
45°	111	87
55°	28	28
65°	6	7
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P211000

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBWGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	438.8
2.5°	435.6
5°	436.7
7.5°	433.5
10°	428.2
12.5°	422.9
15°	415.5
17.5°	409.2
20°	398.6
22.5°	383.8
25°	369.0
27.5°	348.9
30°	322.5
32.5°	292.9
35°	256.9
37.5°	218.9
40°	179.7
42.5°	143.8
45°	111.0
47.5°	83.5
50°	60.3
52.5°	42.3
55°	28.5
57.5°	19.0
60°	13.7
62.5°	9.5
65°	6.3
67.5°	4.2
70°	3.2
72.5°	2.1
75°	1.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)