

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210978

Luminaire Tested: **LSR4B10D010BZ EC4B10209040 4LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210978
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209040 4LBSCMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 972.0 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210978

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBCSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P210978

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	110	106	102	99		108	104	100	97		100	97	94		96	93	91		92	90	89
2	101	94	87	82		99	92	86	81		88	84	79		85	81	78		82	79	76
3	93	83	75	70		90	81	74	69		79	73	68		76	71	67		73	69	65
4	85	74	66	60		83	73	65	59		70	64	58		68	62	58		66	61	57
5	79	66	58	52		77	65	57	51		63	56	51		61	55	50		60	54	50
6	73	60	52	45		71	59	51	45		57	50	45		56	49	44		54	49	44
7	68	55	46	40		66	54	46	40		52	45	40		51	44	40		50	44	39
8	63	50	42	36		61	49	41	36		48	41	36		47	40	36		46	40	35
9	59	46	38	33		57	45	38	32		44	37	32		43	37	32		42	36	32
10	55	42	35	30		54	42	34	30		41	34	29		40	34	29		39	33	29

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210978

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBSCMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.6	3.9
10°-20°	107.1	11.0
20°-30°	161.1	16.6
30°-40°	190.9	19.6
40°-50°	190.0	19.5
50°-60°	153.2	15.8
60°-70°	92.7	9.5
70°-80°	34.4	3.5
80°-90°	5.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	305.8	31.5
0°-40°	496.7	51.1
0°-60°	839.8	86.4
0°-90°	972.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	972.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	397	
5°	395	38
15°	379	107
25°	350	161
35°	306	191
45°	247	190
55°	171	153
65°	93	93
75°	31	34
85°	4	5
90°	0	



TEST NUMBER: P210978

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	397.0
2.5°	397.0
5°	395.2
7.5°	394.0
10°	390.5
12.5°	384.6
15°	379.3
17.5°	373.4
20°	366.3
22.5°	359.3
25°	349.9
27.5°	339.8
30°	328.7
32.5°	318.1
35°	305.7
37.5°	292.7
40°	277.4
42.5°	262.7
45°	247.4
47.5°	230.3
50°	211.4
52.5°	192.0
55°	170.8
57.5°	152.0
60°	130.8
62.5°	111.9
65°	93.1
67.5°	75.4
70°	58.9
72.5°	44.2
75°	31.2
77.5°	20.0
80°	11.8
82.5°	7.1
85°	4.1
87.5°	1.8
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)