

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P210986

Luminaire Tested: **LSR4B10D010BZ EC4B10209040 4LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P210986
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B10D010BZ EC4B10209040 4LBNGPH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-10.05W DE010-10.58W D5LT-10.2W DMX-10.6W DL2-11.8W
DL3-11.1W DLE-11.39W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 436.4 lumens
Efficiency: N/A
Efficacy: 44.1 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210986

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P210986

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P210986

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.6	10.9
10°-20°	119.3	27.3
20°-30°	145.3	33.3
30°-40°	95.9	22.0
40°-50°	22.1	5.1
50°-60°	4.2	1.0
60°-70°	1.6	0.4
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	312.2	71.5
0°-40°	408.1	93.5
0°-60°	434.4	99.5
0°-90°	436.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	436.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	523	
5°	511	48
15°	427	119
25°	319	145
35°	153	96
45°	24	22
55°	4	4
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P210986

CATALOG NUMBER: LSR4B10D010BZ EC4B10209040 4LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	523.3
2.5°	522.2
5°	510.6
7.5°	494.7
10°	473.6
12.5°	452.4
15°	427.1
17.5°	400.6
20°	373.2
22.5°	348.8
25°	319.2
27.5°	289.6
30°	251.6
32.5°	205.1
35°	153.3
37.5°	106.8
40°	68.7
42.5°	42.3
45°	24.3
47.5°	12.7
50°	7.4
52.5°	6.3
55°	4.2
57.5°	3.2
60°	3.2
62.5°	2.1
65°	1.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)