

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211140

Luminaire Tested: **LSR4B15D010BZ EC4B10209027 4LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209027 4LBSLI1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1258.1 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211140

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBSLI1

Luminous Intensity Polar Plot






TEST NUMBER: P211140

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95
2	104	98	93	88	102	96	91	87	93	89	85		90	86	84		87
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		79
4	90	81	73	68	88	79	73	68	77	71	67		75	70	66		73
5	84	73	66	61	82	72	65	60	70	64	60		69	63	59		67
6	79	67	60	54	77	66	59	54	65	58	54		63	58	53		62
7	74	62	54	49	72	61	54	49	60	53	49		58	53	48		57
8	69	57	50	45	68	57	50	45	55	49	45		54	49	44		53
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211140

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.5	6.5
10°-20°	207.7	16.5
20°-30°	269.2	21.4
30°-40°	263.8	21.0
40°-50°	223.6	17.8
50°-60°	146.5	11.6
60°-70°	58.9	4.7
70°-80°	6.7	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.4	44.4
0°-40°	822.1	65.3
0°-60°	1192.2	94.8
0°-90°	1258.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1258.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	898	
5°	875	81
15°	741	208
25°	588	269
35°	419	264
45°	291	224
55°	163	147
65°	57	59
75°	3	7
85°	0	0
90°	0	



TEST NUMBER: P211140

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	898.3
2.5°	891.3
5°	874.6
7.5°	846.8
10°	812.0
12.5°	774.4
15°	740.9
17.5°	704.7
20°	668.5
22.5°	629.5
25°	587.7
27.5°	544.6
30°	500.0
32.5°	458.2
35°	419.2
37.5°	387.2
40°	352.4
42.5°	321.7
45°	291.1
47.5°	259.0
50°	227.0
52.5°	195.0
55°	162.9
57.5°	133.7
60°	105.8
62.5°	80.8
65°	57.1
67.5°	37.6
70°	22.3
72.5°	9.7
75°	2.8
77.5°	1.4
80°	1.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)