

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211133

Luminaire Tested: **LSR4B15D010BZ EC4B10209027 4LBNI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211133
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209027 4LBNLI1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 904.2 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211133

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBNI1

Luminous Intensity Polar Plot






TEST NUMBER: P211133

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211133

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBNI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.4	20.3
10°-20°	313.9	34.7
20°-30°	249.5	27.6
30°-40°	132.1	14.6
40°-50°	22.8	2.5
50°-60°	1.7	0.2
60°-70°	0.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	746.8	82.6
0°-40°	878.9	97.2
0°-60°	903.4	99.9
0°-90°	904.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	904.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2327	
5°	2086	183
15°	1135	314
25°	538	250
35°	209	132
45°	24	23
55°	1	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211133

CATALOG NUMBER: LSR4B15D010BZ EC4B10209027 4LBNLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2326.9
2.5°	2267.0
5°	2086.0
7.5°	1849.3
10°	1598.6
12.5°	1356.3
15°	1134.9
17.5°	928.8
20°	764.5
22.5°	639.2
25°	537.5
27.5°	455.4
30°	373.2
32.5°	289.6
35°	208.9
37.5°	137.9
40°	82.2
42.5°	47.3
45°	23.7
47.5°	8.4
50°	2.8
52.5°	2.8
55°	1.4
57.5°	1.4
60°	1.4
62.5°	1.4
65°	1.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)