

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211156

Luminaire Tested: **LSR4B15D010BZ EC4B10209727 4LBMLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209727 4LBMLI1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1001.5 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211156

CATALOG NUMBER: LSR4B15D010BZ EC4B10209727 4LBML11

Luminous Intensity Polar Plot






TEST NUMBER: P211156

CATALOG NUMBER: LSR4B15D010BZ EC4B10209727 4LBMLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211156

CATALOG NUMBER: LSR4B15D010BZ EC4B10209727 4LBMLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.9	14.3
10°-20°	319.6	31.9
20°-30°	317.7	31.7
30°-40°	173.0	17.3
40°-50°	40.0	4.0
50°-60°	5.6	0.6
60°-70°	2.1	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	780.3	77.9
0°-40°	953.3	95.2
0°-60°	998.9	99.7
0°-90°	1001.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1001.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1579	
5°	1546	143
15°	1154	320
25°	697	318
35°	268	173
45°	46	40
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211156

CATALOG NUMBER: LSR4B15D010BZ EC4B10209727 4LBMLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1578.8
2.5°	1575.2
5°	1546.1
7.5°	1486.7
10°	1404.3
12.5°	1283.2
15°	1153.5
17.5°	1025.1
20°	899.1
22.5°	796.1
25°	696.7
27.5°	602.2
30°	495.6
32.5°	376.8
35°	267.8
37.5°	180.5
40°	117.5
42.5°	73.9
45°	46.0
47.5°	26.7
50°	13.3
52.5°	7.3
55°	6.1
57.5°	3.6
60°	3.6
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)