

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211198

Luminaire Tested: **LSR4B15D010BZ EC4B10208030 4LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211198
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208030 4LBSLI1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1531.2 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211198

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P211198

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102		109	106	103	101		102	100	98		98	96	95		95	93	92
2	104	98	93	88		102	96	91	87		93	89	85		90	86	84		87	84	82
3	97	89	82	77		95	87	81	77		84	79	75		82	78	74		79	76	73
4	90	81	73	68		88	79	73	68		77	71	67		75	70	66		73	69	65
5	84	73	66	61		82	72	65	60		70	64	60		69	63	59		67	62	59
6	79	67	60	54		77	66	59	54		65	58	54		63	58	53		62	57	53
7	74	62	54	49		72	61	54	49		60	53	49		58	53	48		57	52	48
8	69	57	50	45		68	57	50	45		55	49	45		54	49	44		53	48	44
9	65	53	46	41		64	53	46	41		52	45	41		51	45	41		50	44	41
10	61	50	43	38		60	49	42	38		48	42	38		47	42	38		46	41	37

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211198

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.1	6.5
10°-20°	252.8	16.5
20°-30°	327.6	21.4
30°-40°	321.0	21.0
40°-50°	272.1	17.8
50°-60°	178.4	11.6
60°-70°	71.7	4.7
70°-80°	8.2	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	679.6	44.4
0°-40°	1000.6	65.3
0°-60°	1451.1	94.8
0°-90°	1531.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1531.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1093	
5°	1064	99
15°	902	253
25°	715	328
35°	510	321
45°	354	272
55°	198	178
65°	70	72
75°	3	8
85°	0	0
90°	0	



TEST NUMBER: P211198

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1093.4
2.5°	1084.9
5°	1064.5
7.5°	1030.6
10°	988.3
12.5°	942.5
15°	901.8
17.5°	857.7
20°	813.7
22.5°	766.2
25°	715.3
27.5°	662.8
30°	608.6
32.5°	557.7
35°	510.2
37.5°	471.2
40°	428.9
42.5°	391.6
45°	354.3
47.5°	315.3
50°	276.3
52.5°	237.3
55°	198.3
57.5°	162.7
60°	128.8
62.5°	98.3
65°	69.5
67.5°	45.8
70°	27.1
72.5°	11.9
75°	3.4
77.5°	1.7
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)