

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211158

Luminaire Tested: **LSR4B15D010BZ EC4B10209727 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211158
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209727 4LBMWH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 819.8 lumens
Efficiency: N/A
Efficacy: 57.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211158

CATALOG NUMBER: LSR4B15D010BZ EC4B10209727 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211158

CATALOG NUMBER: LSR4B15D010BZ EC4B10209727 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	105		105	103	101		101	100	98		98	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	71	68
7	84	75	69	65		82	74	68	64		73	68	64		72	67	64		70	66	63
8	80	70	64	60		79	70	64	60		69	64	60		68	63	60		67	63	59
9	76	66	61	57		75	66	60	57		65	60	56		64	60	56		63	59	56
10	73	63	57	53		72	62	57	53		62	57	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211158

CATALOG NUMBER: LSR4B15D010BZ EC4B10209727 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	11.0
10°-20°	231.3	28.2
20°-30°	271.3	33.1
30°-40°	171.7	20.9
40°-50°	46.0	5.6
50°-60°	6.4	0.8
60°-70°	2.4	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.5	72.3
0°-40°	764.3	93.2
0°-60°	816.7	99.6
0°-90°	819.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	819.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	974	
5°	958	90
15°	828	231
25°	600	271
35°	272	172
45°	52	46
55°	6	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P211158

CATALOG NUMBER: LSR4B15D010BZ EC4B10209727 4LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	973.7
2.5°	970.0
5°	957.9
7.5°	938.6
10°	910.7
12.5°	874.4
15°	828.3
17.5°	781.1
20°	724.2
22.5°	666.1
25°	599.5
27.5°	526.8
30°	445.7
32.5°	357.3
35°	272.5
37.5°	197.4
40°	135.6
42.5°	87.2
45°	52.1
47.5°	29.1
50°	15.7
52.5°	8.5
55°	6.1
57.5°	4.8
60°	3.6
62.5°	3.6
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)