

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211245

Luminaire Tested: **LSR4B15D010BZ EC4B10209730 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211245
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209730 4LBMWH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 856.8 lumens
Efficiency: N/A
Efficacy: 59.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211245

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211245

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	105		105	103	101		101	100	98		98	96	95
2	108	103	99	96		106	102	98	95		98	95	93		95	93	91		93	91	89
3	103	96	91	88		101	95	90	87		92	89	85		90	87	84		88	85	83
4	98	90	85	81		96	89	84	80		87	83	79		85	81	78		83	80	77
5	93	84	79	74		91	84	78	74		82	77	73		80	76	73		79	75	72
6	88	79	73	69		87	79	73	69		77	72	68		76	71	68		74	71	68
7	84	75	69	65		82	74	68	64		73	68	64		72	67	64		70	66	63
8	80	70	64	60		79	70	64	60		69	64	60		68	63	60		67	63	59
9	76	66	61	57		75	66	60	57		65	60	56		64	60	56		63	59	56
10	73	63	57	53		72	62	57	53		62	57	53		61	56	53		60	56	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211245

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.0	11.0
10°-20°	241.7	28.2
20°-30°	283.5	33.1
30°-40°	179.4	20.9
40°-50°	48.1	5.6
50°-60°	6.7	0.8
60°-70°	2.5	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	619.2	72.3
0°-40°	798.7	93.2
0°-60°	853.5	99.6
0°-90°	856.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	856.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1018	
5°	1001	94
15°	866	242
25°	626	284
35°	285	179
45°	54	48
55°	6	7
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P211245

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1017.6
2.5°	1013.8
5°	1001.1
7.5°	980.9
10°	951.7
12.5°	913.8
15°	865.7
17.5°	816.3
20°	756.8
22.5°	696.1
25°	626.5
27.5°	550.5
30°	465.7
32.5°	373.4
35°	284.8
37.5°	206.3
40°	141.7
42.5°	91.1
45°	54.4
47.5°	30.4
50°	16.5
52.5°	8.9
55°	6.3
57.5°	5.1
60°	3.8
62.5°	3.8
65°	2.5
67.5°	1.3
70°	1.3
72.5°	1.3
75°	1.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)