

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211257

Luminaire Tested: **LSR4B15D010BZ EC4B10209730 4LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211257
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209730 4LBSMW1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1142.8 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211257

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211257

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211257

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	3.8
10°-20°	124.4	10.9
20°-30°	187.3	16.4
30°-40°	222.8	19.5
40°-50°	222.4	19.5
50°-60°	180.9	15.8
60°-70°	111.3	9.7
70°-80°	43.1	3.8
80°-90°	6.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.3	31.1
0°-40°	578.1	50.6
0°-60°	981.5	85.9
0°-90°	1142.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1142.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	459	44
15°	442	124
25°	408	187
35°	357	223
45°	289	222
55°	202	181
65°	112	111
75°	39	43
85°	5	7
90°	0	



TEST NUMBER: P211257

CATALOG NUMBER: LSR4B15D010BZ EC4B10209730 4LBSMW1

CANDELA DISTRIBUTION (FULL):

0°	
0°	460.4
2.5°	461.1
5°	459.1
7.5°	456.4
10°	453.0
12.5°	446.9
15°	441.5
17.5°	433.4
20°	424.6
22.5°	416.4
25°	407.6
27.5°	395.4
30°	383.2
32.5°	371.7
35°	356.8
37.5°	340.6
40°	325.7
42.5°	307.4
45°	289.1
47.5°	269.5
50°	248.5
52.5°	226.8
55°	202.5
57.5°	178.8
60°	155.7
62.5°	133.4
65°	111.7
67.5°	91.4
70°	72.5
72.5°	54.8
75°	39.3
77.5°	25.7
80°	15.6
82.5°	9.5
85°	5.4
87.5°	2.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)