

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211187

Luminaire Tested: **LSR4B15D010BZ EC4B10208030 4LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211187
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208030 4LBMWH1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1148.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.87
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211187

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211187

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	65	82	74	68	64	73	68	64		72	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211187

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.0	11.0
10°-20°	323.8	28.2
20°-30°	379.9	33.1
30°-40°	240.4	20.9
40°-50°	64.4	5.6
50°-60°	9.0	0.8
60°-70°	3.3	0.3
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	829.7	72.3
0°-40°	1070.2	93.2
0°-60°	1143.6	99.6
0°-90°	1148.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1148.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1363	
5°	1341	126
15°	1160	324
25°	839	380
35°	382	240
45°	73	64
55°	8	9
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P211187

CATALOG NUMBER: LSR4B15D010BZ EC4B10208030 4LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1363.4
2.5°	1358.4
5°	1341.4
7.5°	1314.3
10°	1275.3
12.5°	1224.4
15°	1159.9
17.5°	1093.8
20°	1014.1
22.5°	932.7
25°	839.4
27.5°	737.7
30°	624.1
32.5°	500.3
35°	381.6
37.5°	276.4
40°	189.9
42.5°	122.1
45°	72.9
47.5°	40.7
50°	22.0
52.5°	11.9
55°	8.5
57.5°	6.8
60°	5.1
62.5°	5.1
65°	3.4
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)