

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211275

Luminaire Tested: **LSR4B15D010BZ EC4B10208035 4LBN1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P211275  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35248)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR4B15D010BZ EC4B10208035 4LBN1LI  
Description: PORTFOLIO 4 INCH CYLINDER  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1128.0 lumens  
Efficiency: N/A  
Efficacy: 78.9 lumens/watt  
Spacing Criteria (0/90/45): 0.5 / 0.5 / 0.55  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P211275

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBN1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P211275

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBN1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  |  | 102 | 101 | 100 |  |  | 98  |
| 2   | 109 | 105 | 102 | 99  |  | 107 | 103 | 100 | 97  |  | 100 | 98  | 95  |  |  | 97  | 95  | 93  |  |  | 95  |
| 3   | 105 | 99  | 95  | 91  |  | 103 | 98  | 94  | 91  |  | 95  | 92  | 89  |  |  | 93  | 90  | 88  |  |  | 91  |
| 4   | 100 | 94  | 89  | 85  |  | 99  | 93  | 88  | 85  |  | 91  | 87  | 84  |  |  | 89  | 85  | 83  |  |  | 87  |
| 5   | 96  | 89  | 84  | 80  |  | 95  | 88  | 83  | 80  |  | 86  | 82  | 79  |  |  | 85  | 81  | 78  |  |  | 83  |
| 6   | 92  | 85  | 79  | 76  |  | 91  | 84  | 79  | 75  |  | 82  | 78  | 75  |  |  | 81  | 77  | 74  |  |  | 80  |
| 7   | 89  | 81  | 75  | 72  |  | 87  | 80  | 75  | 71  |  | 79  | 74  | 71  |  |  | 78  | 74  | 71  |  |  | 77  |
| 8   | 85  | 77  | 72  | 68  |  | 84  | 76  | 71  | 68  |  | 75  | 71  | 68  |  |  | 74  | 70  | 67  |  |  | 73  |
| 9   | 82  | 73  | 68  | 65  |  | 81  | 73  | 68  | 65  |  | 72  | 68  | 65  |  |  | 71  | 67  | 64  |  |  | 71  |
| 10  | 79  | 70  | 65  | 62  |  | 78  | 70  | 65  | 62  |  | 69  | 65  | 62  |  |  | 68  | 64  | 62  |  |  | 68  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 30210 |
| 5°  | 27716 |
| 10° | 21717 |
| 15° | 15926 |
| 20° | 11018 |
| 25° | 7966  |
| 30° | 5796  |
| 35° | 3518  |
| 40° | 1532  |
| 45° | 489   |
| 50° | 66    |
| 55° | 55    |
| 60° | 41    |
| 65° | 26    |
| 70° | 32    |
| 75° | 0     |
| 80° | 0     |
| 85° | 0     |



TEST NUMBER: P211275

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBN1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 224.4  | 19.9      |
| 10°-20°   | 391.6  | 34.7      |
| 20°-30°   | 310.0  | 27.5      |
| 30°-40°   | 167.7  | 14.9      |
| 40°-50°   | 30.6   | 2.7       |
| 50°-60°   | 2.6    | 0.2       |
| 60°-70°   | 1.1    | 0.1       |
| 70°-80°   | 0.1    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 926.0  | 82.1      |
| 0°-40°    | 1093.7 | 97.0      |
| 0°-60°    | 1126.8 | 99.9      |
| 0°-90°    | 1128.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1128.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2790 |      |
| 5°  | 2550 | 224  |
| 15° | 1421 | 392  |
| 25° | 667  | 310  |
| 35° | 266  | 168  |
| 45° | 32   | 31   |
| 55° | 3    | 3    |
| 65° | 1    | 1    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P211275

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBN1LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 2789.8 |
| 2.5°  | 2741.4 |
| 5°    | 2549.8 |
| 7.5°  | 2270.2 |
| 10°   | 1975.0 |
| 12.5° | 1681.8 |
| 15°   | 1420.6 |
| 17.5° | 1166.1 |
| 20°   | 956.1  |
| 22.5° | 794.5  |
| 25°   | 666.7  |
| 27.5° | 564.2  |
| 30°   | 463.5  |
| 32.5° | 365.8  |
| 35°   | 266.1  |
| 37.5° | 178.1  |
| 40°   | 108.4  |
| 42.5° | 62.9   |
| 45°   | 31.9   |
| 47.5° | 12.6   |
| 50°   | 3.9    |
| 52.5° | 3.9    |
| 55°   | 2.9    |
| 57.5° | 1.9    |
| 60°   | 1.9    |
| 62.5° | 1.0    |
| 65°   | 1.0    |
| 67.5° | 1.0    |
| 70°   | 1.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)