

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211280

Luminaire Tested: **LSR4B15D010BZ EC4B10208035 4LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211280
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208035 4LBNWH1
Description: PORTFOLIO 4 INCH CYLINDER
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1006.5 lumens
Efficiency: N/A
Efficacy: 70.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.62
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211280

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211280

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95						
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89						
3	104	98	94	90	102	97	93	90	94	91	88	92	89	87	90	87	85	84						
4	100	93	88	84	98	92	87	83	90	86	82	88	84	82	86	83	81	79						
5	95	88	82	78	94	87	82	78	85	81	77	83	80	77	82	79	76	75						
6	91	83	78	74	90	82	77	74	81	76	73	79	76	73	78	75	72	71						
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67						
8	84	75	70	66	82	74	69	66	73	69	65	72	68	65	71	68	65	64						
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	65	62	61						
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	66	62	59	58						

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211280

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.9	17.4
10°-20°	328.1	32.6
20°-30°	294.4	29.3
30°-40°	168.9	16.8
40°-50°	33.7	3.3
50°-60°	4.3	0.4
60°-70°	1.9	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.4	79.2
0°-40°	966.4	96.0
0°-60°	1004.3	99.8
0°-90°	1006.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1006.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2139	
5°	1967	175
15°	1178	328
25°	636	294
35°	268	169
45°	36	34
55°	5	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P211280

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBNWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2139.0
2.5°	2095.6
5°	1967.0
7.5°	1779.3
10°	1574.3
12.5°	1372.7
15°	1178.1
17.5°	1007.8
20°	861.9
22.5°	740.2
25°	636.0
27.5°	552.6
30°	460.5
32.5°	366.6
35°	267.6
37.5°	182.4
40°	112.9
42.5°	67.8
45°	36.5
47.5°	15.6
50°	7.0
52.5°	5.2
55°	5.2
57.5°	3.5
60°	3.5
62.5°	1.7
65°	1.7
67.5°	1.7
70°	1.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)