

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211316

Luminaire Tested: **LSR4B15D010BZ EC4B10209035 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211316
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209035 4LBSWH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1279.0 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211316

CATALOG NUMBER: LSR4B15D010BZ EC4B10209035 4LBSWH1

Luminous Intensity Polar Plot






TEST NUMBER: P211316

CATALOG NUMBER: LSR4B15D010BZ EC4B10209035 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211316

CATALOG NUMBER: LSR4B15D010BZ EC4B10209035 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.4	5.5
10°-20°	182.1	14.2
20°-30°	238.2	18.6
30°-40°	252.2	19.7
40°-50°	235.2	18.4
50°-60°	178.2	13.9
60°-70°	96.5	7.5
70°-80°	25.9	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	490.7	38.4
0°-40°	742.9	58.1
0°-60°	1156.2	90.4
0°-90°	1279.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1279.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	763	
5°	752	70
15°	651	182
25°	518	238
35°	403	252
45°	306	235
55°	200	178
65°	97	97
75°	22	26
85°	0	0
90°	0	



TEST NUMBER: P211316

CATALOG NUMBER: LSR4B15D010BZ EC4B10209035 4LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	762.8
2.5°	760.0
5°	751.6
7.5°	733.4
10°	709.6
12.5°	681.6
15°	650.8
17.5°	615.8
20°	585.1
22.5°	550.1
25°	517.9
27.5°	485.7
30°	454.9
32.5°	428.3
35°	403.1
37.5°	377.9
40°	354.1
42.5°	330.3
45°	306.5
47.5°	279.9
50°	253.3
52.5°	226.7
55°	200.1
57.5°	172.2
60°	145.6
62.5°	120.4
65°	96.6
67.5°	74.2
70°	54.6
72.5°	37.8
75°	22.4
77.5°	9.8
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)