

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211349

Luminaire Tested: **LSR4B15D010BZ EC4B10208040 4LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211349
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208040 4LBWH1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1294.8 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211349

CATALOG NUMBER: LSR4B15D010BZ EC4B10208040 4LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P211349

CATALOG NUMBER: LSR4B15D010BZ EC4B10208040 4LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211349

CATALOG NUMBER: LSR4B15D010BZ EC4B10208040 4LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.5	6.1
10°-20°	229.0	17.7
20°-30°	337.9	26.1
30°-40°	333.5	25.8
40°-50°	204.1	15.8
50°-60°	78.3	6.0
60°-70°	24.4	1.9
70°-80°	7.2	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	646.4	49.9
0°-40°	979.9	75.7
0°-60°	1262.2	97.5
0°-90°	1294.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1294.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	834	
5°	834	79
15°	812	229
25°	740	338
35°	541	333
45°	262	204
55°	83	78
65°	23	24
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P211349

CATALOG NUMBER: LSR4B15D010BZ EC4B10208040 4LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	834.5
2.5°	836.3
5°	834.5
7.5°	832.8
10°	827.5
12.5°	820.5
15°	811.7
17.5°	801.2
20°	785.3
22.5°	767.8
25°	739.7
27.5°	704.5
30°	660.6
32.5°	606.1
35°	541.1
37.5°	469.1
40°	395.3
42.5°	326.8
45°	261.8
47.5°	203.8
50°	154.6
52.5°	114.2
55°	82.6
57.5°	58.0
60°	42.2
62.5°	31.6
65°	22.8
67.5°	17.6
70°	12.3
72.5°	8.8
75°	7.0
77.5°	3.5
80°	3.5
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)