

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211293

Luminaire Tested: **LSR4B15D010BZ EC4B10208035 4LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211293
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208035 4LBWMW1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1338.5 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211293

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211293

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		93	92	90
2	103	96	91	86		101	94	89	85		91	87	83		88	84	81		85	82	80
3	96	87	80	75		93	85	79	74		83	77	73		80	76	72		78	74	71
4	89	79	72	66		87	78	71	66		75	69	65		73	68	64		71	67	63
5	83	72	64	59		81	71	64	58		69	63	58		67	62	57		65	61	57
6	78	66	58	53		76	65	58	53		64	57	52		62	56	52		60	55	51
7	73	61	53	48		71	60	53	48		59	52	47		57	51	47		56	51	47
8	68	56	49	44		67	56	49	44		54	48	43		53	47	43		52	47	43
9	64	52	45	40		63	52	45	40		51	44	40		50	44	40		49	43	39
10	61	49	42	37		59	48	41	37		47	41	37		46	41	37		46	40	36

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211293

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.2	5.7
10°-20°	213.0	15.9
20°-30°	301.0	22.5
30°-40°	291.5	21.8
40°-50°	196.7	14.7
50°-60°	122.1	9.1
60°-70°	81.6	6.1
70°-80°	44.6	3.3
80°-90°	11.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.1	44.1
0°-40°	881.6	65.9
0°-60°	1200.4	89.7
0°-90°	1338.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1338.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	811	
5°	804	76
15°	756	213
25°	660	301
35°	469	292
45°	252	197
55°	134	122
65°	82	82
75°	42	45
85°	10	12
90°	0	



TEST NUMBER: P211293

CATALOG NUMBER: LSR4B15D010BZ EC4B10208035 4LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	811.1
2.5°	811.1
5°	804.1
7.5°	795.5
10°	785.0
12.5°	774.6
15°	755.5
17.5°	739.9
20°	713.8
22.5°	687.8
25°	660.0
27.5°	621.8
30°	580.1
32.5°	526.3
35°	468.9
37.5°	411.6
40°	354.3
42.5°	297.0
45°	251.8
47.5°	210.2
50°	178.9
52.5°	152.8
55°	133.7
57.5°	118.1
60°	105.9
62.5°	93.8
65°	81.6
67.5°	71.2
70°	60.8
72.5°	52.1
75°	41.7
77.5°	33.0
80°	24.3
82.5°	17.4
85°	10.4
87.5°	3.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)