

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211418

Luminaire Tested: **LSR4B15D010BZ EC4B10209050 4LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209050 4LBMMW1
Description: PORTFOLIO 4 INCH CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1019.4 lumens
Efficiency: N/A
Efficacy: 71.3 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211418

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P211418

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	102		109	106	103	100		102	99	97		98	96	94		94	93	91
2	104	98	92	88		102	96	91	87		93	89	85		89	86	83		87	84	81
3	97	89	83	77		95	87	82	77		85	80	76		82	78	74		80	76	73
4	91	81	74	69		89	80	74	69		78	72	68		76	71	67		74	69	66
5	85	75	67	62		83	74	67	62		72	66	61		70	65	61		68	64	60
6	80	69	62	56		78	68	61	56		66	60	56		65	59	55		63	59	55
7	75	64	57	52		74	63	56	51		62	56	51		60	55	51		59	54	50
8	71	59	52	47		69	59	52	47		58	51	47		56	51	47		55	50	47
9	67	55	48	44		66	55	48	44		54	48	44		53	47	43		52	47	43
10	63	52	45	41		62	51	45	41		51	45	40		50	44	40		49	44	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211418

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.7	7.0
10°-20°	192.3	18.9
20°-30°	255.7	25.1
30°-40°	209.1	20.5
40°-50°	121.8	11.9
50°-60°	80.8	7.9
60°-70°	53.1	5.2
70°-80°	28.0	2.8
80°-90°	6.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.7	51.0
0°-40°	728.9	71.5
0°-60°	931.4	91.4
0°-90°	1019.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1019.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	774	
5°	765	72
15°	685	192
25°	561	256
35°	334	209
45°	154	122
55°	90	81
65°	53	53
75°	27	28
85°	6	7
90°	0	



TEST NUMBER: P211418

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	773.9
2.5°	772.4
5°	765.0
7.5°	747.3
10°	728.1
12.5°	710.4
15°	685.3
17.5°	657.2
20°	633.6
22.5°	601.1
25°	561.2
27.5°	518.4
30°	463.7
32.5°	398.7
35°	333.8
37.5°	274.7
40°	223.0
42.5°	183.1
45°	153.6
47.5°	130.0
50°	113.7
52.5°	100.4
55°	90.1
57.5°	79.7
60°	69.4
62.5°	62.0
65°	53.2
67.5°	45.8
70°	38.4
72.5°	32.5
75°	26.6
77.5°	20.7
80°	14.8
82.5°	10.3
85°	5.9
87.5°	1.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)