

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211321

Luminaire Tested: **LSR4B15D010BZ EC4B10209035 4LBWLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211321
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209035 4LBWLI1
Description: PORTFOLIO 4 INCH CYLINDER
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1282.6 lumens
Efficiency: N/A
Efficacy: 89.7 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211321

CATALOG NUMBER: LSR4B15D010BZ EC4B10209035 4LBWL11

Luminous Intensity Polar Plot





TEST NUMBER: P211321

CATALOG NUMBER: LSR4B15D010BZ EC4B10209035 4LBWLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211321

CATALOG NUMBER: LSR4B15D010BZ EC4B10209035 4LBWLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.8	6.0
10°-20°	242.5	18.9
20°-30°	378.3	29.5
30°-40°	368.1	28.7
40°-50°	183.9	14.3
50°-60°	28.5	2.2
60°-70°	3.4	0.3
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.7	54.4
0°-40°	1065.8	83.1
0°-60°	1278.1	99.7
0°-90°	1282.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1282.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	786	
5°	796	77
15°	856	243
25°	831	378
35°	598	368
45°	231	184
55°	24	28
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P211321

CATALOG NUMBER: LSR4B15D010BZ EC4B10209035 4LBWLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	785.8
2.5°	788.8
5°	796.1
7.5°	807.9
10°	822.5
12.5°	841.6
15°	856.3
17.5°	868.1
20°	869.5
22.5°	859.3
25°	831.4
27.5°	790.2
30°	738.8
32.5°	674.2
35°	597.8
37.5°	514.1
40°	426.0
42.5°	332.0
45°	230.6
47.5°	148.4
50°	89.6
52.5°	48.5
55°	23.5
57.5°	10.3
60°	5.9
62.5°	4.4
65°	2.9
67.5°	2.9
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)