

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211430

Luminaire Tested: **LSR4B15D010BZ EC4B10209050 4LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211430
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209050 4LBSLI1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1334.2 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211430

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P211430

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95
2	104	98	93	88	102	96	91	87	93	89	85		90	86	84		87
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		79
4	90	81	73	68	88	79	73	68	77	71	67		75	70	66		73
5	84	73	66	61	82	72	65	60	70	64	60		69	63	59		67
6	79	67	60	54	77	66	59	54	65	58	54		63	58	53		62
7	74	62	54	49	72	61	54	49	60	53	49		58	53	48		57
8	69	57	50	45	68	57	50	45	55	49	45		54	49	44		53
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211430

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.4	6.5
10°-20°	220.3	16.5
20°-30°	285.5	21.4
30°-40°	279.7	21.0
40°-50°	237.1	17.8
50°-60°	155.4	11.6
60°-70°	62.5	4.7
70°-80°	7.2	0.5
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	592.1	44.4
0°-40°	871.8	65.3
0°-60°	1264.3	94.8
0°-90°	1334.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1334.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	953	
5°	928	86
15°	786	220
25°	623	285
35°	444	280
45°	309	237
55°	173	155
65°	61	62
75°	3	7
85°	0	0
90°	0	



TEST NUMBER: P211430

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	952.6
2.5°	945.2
5°	927.5
7.5°	897.9
10°	861.0
12.5°	821.1
15°	785.7
17.5°	747.3
20°	708.9
22.5°	667.6
25°	623.2
27.5°	577.5
30°	530.2
32.5°	485.9
35°	444.5
37.5°	410.6
40°	373.7
42.5°	341.2
45°	308.7
47.5°	274.7
50°	240.7
52.5°	206.8
55°	172.8
57.5°	141.8
60°	112.2
62.5°	85.7
65°	60.6
67.5°	39.9
70°	23.6
72.5°	10.3
75°	3.0
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)