

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432288

Luminaire Tested: **LAM4B108R559024DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432288
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-898-142)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B108R559024DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 55 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 700.8 lumens
Efficiency: N/A
Efficacy: 61.5 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432288

CATALOG NUMBER: LAM4B108R559024DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P432288

CATALOG NUMBER: LAM4B108R559024DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107		112	110	108	106		105	104	102		102	101	99		98	97	97
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85		99	92	88	85		90	87	84		88	85	83		87	84	82
5	96	89	83	80		94	88	83	79		86	82	79		84	81	78		83	80	77
6	92	84	79	75		91	83	78	75		82	78	74		81	77	74		79	76	73
7	88	80	75	71		87	79	74	71		78	74	70		77	73	70		76	72	70
8	84	76	71	67		83	75	70	67		74	70	67		73	69	66		72	69	66
9	81	72	67	64		80	72	67	63		71	66	63		70	66	63		69	66	63
10	78	69	64	60		77	69	64	60		68	63	60		67	63	60		66	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	471671
5°	478277
10°	489468
15°	469002
20°	426125
25°	342418
30°	197118
35°	57219
40°	8759
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P432288

CATALOG NUMBER: LAM4B108R559024DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.6	13.2
10°-20°	255.5	36.5
20°-30°	275.7	39.3
30°-40°	75.4	10.8
40°-50°	1.6	0.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	623.8	89.0
0°-40°	699.2	99.8
0°-60°	700.8	100.0
0°-90°	700.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	700.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	956	
5°	966	93
15°	918	255
25°	629	276
35°	95	75
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P432288

CATALOG NUMBER: LAM4B108R559024DE010x1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	956.0
2.5°	952.1
5°	965.7
7.5°	976.4
10°	977.0
12.5°	952.1
15°	918.2
17.5°	873.3
20°	811.6
22.5°	732.1
25°	629.0
27.5°	497.6
30°	346.0
32.5°	189.7
35°	95.0
37.5°	40.7
40°	13.6
42.5°	1.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)