

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211403

Luminaire Tested: **LSR4B15D010BZ EC4B10208050 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10208050 4LBSWH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1528.8 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211403

CATALOG NUMBER: LSR4B15D010BZ EC4B10208050 4LBSWH1

Luminous Intensity Polar Plot






TEST NUMBER: P211403

CATALOG NUMBER: LSR4B15D010BZ EC4B10208050 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211403

CATALOG NUMBER: LSR4B15D010BZ EC4B10208050 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.1	5.5
10°-20°	217.7	14.2
20°-30°	284.7	18.6
30°-40°	301.5	19.7
40°-50°	281.2	18.4
50°-60°	213.0	13.9
60°-70°	115.3	7.5
70°-80°	30.9	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	586.4	38.4
0°-40°	887.9	58.1
0°-60°	1382.0	90.4
0°-90°	1528.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1528.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	912	
5°	898	84
15°	778	218
25°	619	285
35°	482	301
45°	366	281
55°	239	213
65°	115	115
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P211403

CATALOG NUMBER: LSR4B15D010BZ EC4B10208050 4LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	911.7
2.5°	908.4
5°	898.3
7.5°	876.6
10°	848.1
12.5°	814.7
15°	777.9
17.5°	736.1
20°	699.3
22.5°	657.4
25°	619.0
27.5°	580.5
30°	543.7
32.5°	511.9
35°	481.8
37.5°	451.7
40°	423.2
42.5°	394.8
45°	366.4
47.5°	334.6
50°	302.8
52.5°	271.0
55°	239.2
57.5°	205.8
60°	174.0
62.5°	143.9
65°	115.4
67.5°	88.7
70°	65.2
72.5°	45.2
75°	26.8
77.5°	11.7
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)