

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432360

Luminaire Tested: **LAM4B108R709024DE010x1MW**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B108R709024DE010x1MW
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 679.1 lumens
Efficiency: N/A
Efficacy: 59.6 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432360

CATALOG NUMBER: LAM4B108R709024DE010x1MW

Luminous Intensity Polar Plot





TEST NUMBER: P432360

CATALOG NUMBER: LAM4B108R709024DE010x1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	64	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54		
8	74	63	57	52	73	63	56	52	62	56	52	60	55	51	59	55	51	50		
9	70	59	52	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46		
10	66	55	49	45	65	55	49	44	54	48	44	53	48	44	52	48	44	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	246246
5°	241689
10°	244483
15°	251357
20°	251811
25°	228424
30°	204126
35°	179306
40°	131968
45°	73961
50°	36382
55°	20386
60°	12334
65°	8172
70°	6059
75°	5338
80°	3978
85°	3963



TEST NUMBER: P432360

CATALOG NUMBER: LAM4B108R709024DE010x1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.6	6.9
10°-20°	138.7	20.4
20°-30°	192.4	28.3
30°-40°	181.1	26.7
40°-50°	86.4	12.7
50°-60°	22.8	3.4
60°-70°	7.2	1.1
70°-80°	3.0	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	377.8	55.6
0°-40°	558.8	82.3
0°-60°	668.1	98.4
0°-90°	679.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	679.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	499	
5°	488	47
15°	492	139
25°	420	192
35°	298	181
45°	106	86
55°	24	23
65°	7	7
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P432360

CATALOG NUMBER: LAM4B108R709024DE010x1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	499.1
2.5°	492.8
5°	488.0
7.5°	487.3
10°	488.0
12.5°	489.4
15°	492.1
17.5°	492.1
20°	479.6
22.5°	453.1
25°	419.6
27.5°	386.2
30°	358.3
32.5°	331.1
35°	297.7
37.5°	254.4
40°	204.9
42.5°	152.7
45°	106.0
47.5°	70.4
50°	47.4
52.5°	32.8
55°	23.7
57.5°	16.7
60°	12.5
62.5°	9.1
65°	7.0
67.5°	4.9
70°	4.2
72.5°	3.5
75°	2.8
77.5°	2.1
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)