

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433414

Luminaire Tested: **LAMR4B108R309024DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R309024DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 707.1 lumens
Efficiency: N/A
Efficacy: 62.0 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433414

CATALOG NUMBER: LAMR4B108R309024DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P433414

CATALOG NUMBER: LAMR4B108R309024DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96		
2	111	107	104	102	109	106	103	100	102	100	98	100	98	96	97	95	94	93		
3	107	103	99	96	105	101	98	95	99	96	94	96	94	92	94	92	91	90		
4	104	98	94	91	102	97	94	91	95	92	90	93	91	89	92	90	88	87		
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84		
6	98	91	87	84	97	91	87	84	89	86	83	88	85	83	87	84	82	81		
7	95	88	84	81	94	88	84	81	87	83	81	86	83	80	85	82	80	79		
8	92	86	81	79	91	85	81	78	84	81	78	83	80	78	83	80	78	77		
9	90	83	79	76	89	83	79	76	82	78	76	81	78	76	80	78	75	74		
10	88	81	77	74	87	80	76	74	80	76	74	79	76	74	78	76	73	72		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1281011
5°	1253018
10°	1086448
15°	673367
20°	246823
25°	82474
30°	40506
35°	20177
40°	12495
45°	7954
50°	5680
55°	4645
60°	3947
65°	3152
70°	3895
75°	3813
80°	3694
85°	3963



TEST NUMBER: P433414

CATALOG NUMBER: LAMR4B108R309024DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.6	32.6
10°-20°	348.1	49.2
20°-30°	84.9	12.0
30°-40°	23.2	3.3
40°-50°	9.4	1.3
50°-60°	5.0	0.7
60°-70°	3.0	0.4
70°-80°	2.3	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	663.6	93.9
0°-40°	686.8	97.1
0°-60°	701.2	99.2
0°-90°	707.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	707.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2596	
5°	2530	231
15°	1318	348
25°	152	85
35°	34	23
45°	11	9
55°	5	5
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P433414

CATALOG NUMBER: LAMR4B108R309024DE010x1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2596.4
2.5°	2579.0
5°	2530.0
7.5°	2413.4
10°	2168.6
12.5°	1785.0
15°	1318.3
17.5°	849.6
20°	470.1
22.5°	250.8
25°	151.5
27.5°	102.6
30°	71.1
32.5°	48.3
35°	33.5
37.5°	24.8
40°	19.4
42.5°	14.8
45°	11.4
47.5°	9.4
50°	7.4
52.5°	6.7
55°	5.4
57.5°	4.7
60°	4.0
62.5°	3.4
65°	2.7
67.5°	2.7
70°	2.7
72.5°	2.7
75°	2.0
77.5°	2.0
80°	1.3
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)