

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P211432

Luminaire Tested: **LSR4B15D010BZ EC4B10209050 4LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P211432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR4B15D010BZ EC4B10209050 4LBSWH1
Description: PORTFOLIO 4 INCH CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39W DE010-14.29W D5LT-14.34W DMX-14.46W DL2-15.8W
DL3-15.28W DLE-15.432W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1286.3 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P211432

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSWH1

Luminous Intensity Polar Plot






TEST NUMBER: P211432

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73		93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64		86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56		79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45		69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41		65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37		61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34		57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P211432

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.8	5.5
10°-20°	183.1	14.2
20°-30°	239.5	18.6
30°-40°	253.6	19.7
40°-50°	236.6	18.4
50°-60°	179.2	13.9
60°-70°	97.1	7.5
70°-80°	26.0	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.4	38.4
0°-40°	747.1	58.1
0°-60°	1162.8	90.4
0°-90°	1286.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1286.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	767	
5°	756	71
15°	654	183
25°	521	240
35°	405	254
45°	308	237
55°	201	179
65°	97	97
75°	22	26
85°	0	0
90°	0	



TEST NUMBER: P211432

CATALOG NUMBER: LSR4B15D010BZ EC4B10209050 4LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	767.1
2.5°	764.3
5°	755.9
7.5°	737.6
10°	713.6
12.5°	685.5
15°	654.5
17.5°	619.3
20°	588.4
22.5°	553.2
25°	520.8
27.5°	488.4
30°	457.5
32.5°	430.7
35°	405.4
37.5°	380.0
40°	356.1
42.5°	332.2
45°	308.3
47.5°	281.5
50°	254.8
52.5°	228.0
55°	201.3
57.5°	173.1
60°	146.4
62.5°	121.1
65°	97.1
67.5°	74.6
70°	54.9
72.5°	38.0
75°	22.5
77.5°	9.9
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)