

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433487

Luminaire Tested: **LAMR4B108R459024DE010x1MMS**

Issue Date: 11/23/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P433487  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)  
Test Lab: INNOVATION CENTER (G2)  
Issue Date: 11/23/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LAMR4B108R459024DE010x1MMS  
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC  
Light Source: HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 699.7 lumens  
Efficiency: N/A  
Efficacy: 61.4 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P433487

CATALOG NUMBER: LAMR4B108R459024DE010x1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P433487

CATALOG NUMBER: LAMR4B108R459024DE010x1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 109 | 107 |  | 112 | 109 | 107 | 105 |  | 105 | 104 | 102 |  | 102 | 100 | 99  |  | 98  | 97  | 96  |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 93  | 91  |
| 3   | 105 | 99  | 94  | 91  |  | 103 | 98  | 93  | 90  |  | 95  | 92  | 89  |  | 93  | 90  | 87  |  | 90  | 88  | 86  |
| 4   | 100 | 94  | 89  | 85  |  | 99  | 93  | 88  | 85  |  | 90  | 87  | 84  |  | 89  | 85  | 83  |  | 87  | 84  | 82  |
| 5   | 96  | 89  | 84  | 80  |  | 95  | 88  | 83  | 80  |  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 78  |
| 6   | 92  | 85  | 79  | 76  |  | 91  | 84  | 79  | 75  |  | 82  | 78  | 75  |  | 81  | 77  | 74  |  | 80  | 77  | 74  |
| 7   | 89  | 81  | 75  | 72  |  | 87  | 80  | 75  | 72  |  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 71  |
| 8   | 85  | 77  | 72  | 68  |  | 84  | 77  | 72  | 68  |  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 67  |
| 9   | 82  | 74  | 69  | 65  |  | 81  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 67  | 65  |
| 10  | 79  | 71  | 66  | 62  |  | 78  | 70  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 62  |  | 68  | 65  | 62  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 646574 |
| 5°  | 646369 |
| 10° | 614365 |
| 15° | 539643 |
| 20° | 412842 |
| 25° | 240999 |
| 30° | 98616  |
| 35° | 41740  |
| 40° | 22735  |
| 45° | 14653  |
| 50° | 11437  |
| 55° | 9892   |
| 60° | 7993   |
| 65° | 6304   |
| 70° | 5914   |
| 75° | 5147   |
| 80° | 5683   |
| 85° | 3963   |



TEST NUMBER: P433487

CATALOG NUMBER: LAMR4B108R459024DE010x1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 122.1  | 17.5      |
| 10°-20°   | 287.6  | 41.1      |
| 20°-30°   | 202.7  | 29.0      |
| 30°-40°   | 49.9   | 7.1       |
| 40°-50°   | 17.4   | 2.5       |
| 50°-60°   | 10.3   | 1.5       |
| 60°-70°   | 5.7    | 0.8       |
| 70°-80°   | 3.1    | 0.4       |
| 80°-90°   | 0.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 612.4  | 87.5      |
| 0°-40°    | 662.3  | 94.7      |
| 0°-60°    | 690.0  | 98.6      |
| 0°-90°    | 699.7  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 699.7  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1310 |      |
| 5°  | 1305 | 122  |
| 15° | 1056 | 288  |
| 25° | 443  | 203  |
| 35° | 69   | 50   |
| 45° | 21   | 17   |
| 55° | 12   | 10   |
| 65° | 5    | 6    |
| 75° | 3    | 3    |
| 85° | 1    | 1    |
| 90° | 0    |      |



TEST NUMBER: P433487

CATALOG NUMBER: LAMR4B108R459024DE010x1MMS

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1310.5 |
| 2.5°  | 1307.1 |
| 5°    | 1305.1 |
| 7.5°  | 1281.3 |
| 10°   | 1226.3 |
| 12.5° | 1151.6 |
| 15°   | 1056.5 |
| 17.5° | 933.6  |
| 20°   | 786.3  |
| 22.5° | 617.2  |
| 25°   | 442.7  |
| 27.5° | 285.9  |
| 30°   | 173.1  |
| 32.5° | 105.2  |
| 35°   | 69.3   |
| 37.5° | 48.9   |
| 40°   | 35.3   |
| 42.5° | 27.2   |
| 45°   | 21.0   |
| 47.5° | 17.7   |
| 50°   | 14.9   |
| 52.5° | 12.9   |
| 55°   | 11.5   |
| 57.5° | 10.2   |
| 60°   | 8.1    |
| 62.5° | 6.8    |
| 65°   | 5.4    |
| 67.5° | 4.8    |
| 70°   | 4.1    |
| 72.5° | 3.4    |
| 75°   | 2.7    |
| 77.5° | 2.7    |
| 80°   | 2.0    |
| 82.5° | 1.4    |
| 85°   | 0.7    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)