

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433418

Luminaire Tested: **LAMR4B108R309027DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R309027DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 771.1 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433418

CATALOG NUMBER: LAMR4B108R309027DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433418

CATALOG NUMBER: LAMR4B108R309027DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97
3	107	103	99	96	105	101	98	95	99	96	94		96	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		93	91	89		92
5	101	95	91	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	97	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	88	84	81	87	83	81		86	83	80		85
8	92	86	81	79	91	85	81	78	84	81	78		83	80	78		83
9	90	83	79	76	89	83	79	76	82	78	76		81	78	76		80
10	88	81	77	74	87	80	77	74	80	76	74		79	76	74		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1397202
5°	1366682
10°	1184993
15°	734456
20°	269190
25°	89987
30°	44152
35°	22044
40°	13654
45°	8652
50°	6140
55°	5075
60°	4342
65°	3386
70°	4183
75°	4194
80°	4262
85°	3963



TEST NUMBER: P433418

CATALOG NUMBER: LAMR4B108R309027DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.5	32.6
10°-20°	379.7	49.2
20°-30°	92.6	12.0
30°-40°	25.4	3.3
40°-50°	10.2	1.3
50°-60°	5.5	0.7
60°-70°	3.3	0.4
70°-80°	2.5	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.8	93.9
0°-40°	749.1	97.1
0°-60°	764.8	99.2
0°-90°	771.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	771.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2832	
5°	2760	251
15°	1438	380
25°	165	93
35°	37	25
45°	12	10
55°	6	5
65°	3	3
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P433418

CATALOG NUMBER: LAMR4B108R309027DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2831.9
2.5°	2812.9
5°	2759.5
7.5°	2632.2
10°	2365.3
12.5°	1946.9
15°	1437.9
17.5°	926.7
20°	512.7
22.5°	273.5
25°	165.3
27.5°	111.9
30°	77.5
32.5°	52.7
35°	36.6
37.5°	27.1
40°	21.2
42.5°	16.1
45°	12.4
47.5°	10.2
50°	8.0
52.5°	7.3
55°	5.9
57.5°	5.1
60°	4.4
62.5°	3.7
65°	2.9
67.5°	2.9
70°	2.9
72.5°	2.9
75°	2.2
77.5°	2.2
80°	1.5
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)