

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P432244

Luminaire Tested: **LAM4B108R459030DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P432244
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2008-908-8)
Test Lab: INNOVATION CENTER (G2)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAM4B108R459030DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 45 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 784.9 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.66
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P432244

CATALOG NUMBER: LAM4B108R459030DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P432244

CATALOG NUMBER: LAM4B108R459030DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	94	91	103	98	93	90	95	92	89		93	90	87		90
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	78		83
6	92	85	79	76	91	84	79	75	82	78	75		81	77	74		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	66	62	70	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	725317
5°	725067
10°	689213
15°	605381
20°	463141
25°	270341
30°	110637
35°	46799
40°	25505
45°	16467
50°	12895
55°	11096
60°	8980
65°	7121
70°	6636
75°	5719
80°	6535
85°	4529



TEST NUMBER: P432244

CATALOG NUMBER: LAM4B108R459030DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.0	17.5
10°-20°	322.7	41.1
20°-30°	227.3	29.0
30°-40°	56.0	7.1
40°-50°	19.5	2.5
50°-60°	11.5	1.5
60°-70°	6.4	0.8
70°-80°	3.5	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.0	87.5
0°-40°	743.0	94.7
0°-60°	774.1	98.6
0°-90°	784.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	784.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1470	
5°	1464	137
15°	1185	323
25°	497	227
35°	78	56
45°	24	20
55°	13	12
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P432244

CATALOG NUMBER: LAM4B108R459030DE010x1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1470.1
2.5°	1466.3
5°	1464.0
7.5°	1437.4
10°	1375.7
12.5°	1291.9
15°	1185.2
17.5°	1047.4
20°	882.1
22.5°	692.4
25°	496.6
27.5°	320.7
30°	194.2
32.5°	118.1
35°	77.7
37.5°	54.8
40°	39.6
42.5°	30.5
45°	23.6
47.5°	19.8
50°	16.8
52.5°	14.5
55°	12.9
57.5°	11.4
60°	9.1
62.5°	7.6
65°	6.1
67.5°	5.3
70°	4.6
72.5°	3.8
75°	3.0
77.5°	3.0
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)