

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433421

Luminaire Tested: **LAMR4B108R309030DE010x1MMS**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-8)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R309030DE010x1MMS
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 30 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 793.2 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.46
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433421

CATALOG NUMBER: LAMR4B108R309030DE010x1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P433421

CATALOG NUMBER: LAMR4B108R309030DE010x1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	111	109	107	107	105	104		103	102	101		100
2	111	107	104	102	109	106	103	100	102	100	98		100	98	96		97
3	107	103	99	96	105	101	98	95	99	96	94		96	94	92		94
4	104	98	94	91	102	97	94	91	95	92	90		93	91	89		92
5	101	95	90	87	99	94	90	87	92	89	86		91	88	86		89
6	98	91	87	84	97	91	87	84	89	86	83		88	85	83		87
7	95	88	84	81	94	88	84	81	87	83	81		86	83	80		85
8	92	86	81	79	91	85	81	78	84	81	78		83	80	78		83
9	90	83	79	76	89	83	79	76	82	78	76		81	78	76		80
10	88	81	77	74	87	80	77	74	80	76	74		79	76	74		78

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1437067
5°	1405659
10°	1218810
15°	755399
20°	276855
25°	92545
30°	45406
35°	22647
40°	14041
45°	8931
50°	6371
55°	5161
60°	4440
65°	3502
70°	4328
75°	4384
80°	4262
85°	4529



TEST NUMBER: P433421

CATALOG NUMBER: LAMR4B108R309030DE010x1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.7	32.6
10°-20°	390.5	49.2
20°-30°	95.2	12.0
30°-40°	26.1	3.3
40°-50°	10.5	1.3
50°-60°	5.6	0.7
60°-70°	3.4	0.4
70°-80°	2.6	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	744.4	93.9
0°-40°	770.5	97.1
0°-60°	786.6	99.2
0°-90°	793.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2913	
5°	2838	259
15°	1479	391
25°	170	95
35°	38	26
45°	13	10
55°	6	6
65°	3	3
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P433421

CATALOG NUMBER: LAMR4B108R309030DE010x1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2912.7
2.5°	2893.1
5°	2838.2
7.5°	2707.3
10°	2432.8
12.5°	2002.5
15°	1478.9
17.5°	953.1
20°	527.3
22.5°	281.3
25°	170.0
27.5°	115.1
30°	79.7
32.5°	54.2
35°	37.6
37.5°	27.8
40°	21.8
42.5°	16.5
45°	12.8
47.5°	10.5
50°	8.3
52.5°	7.5
55°	6.0
57.5°	5.3
60°	4.5
62.5°	3.8
65°	3.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	2.3
77.5°	2.3
80°	1.5
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)