

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P433612

Luminaire Tested: **LAMR4B108R709030DE010x1MB**

Issue Date: 11/23/2020

Test Information

Test Method: LM-41-14
Report Number: P433612
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2007-857-14)
Test Lab: INNOVATION CENTER (G1)
Issue Date: 11/23/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LAMR4B108R709030DE010x1MB
Description: PORTFOLIO 4INCH ADJUSTABLE MULTIPLE, 70 DEG TIR OPTIC
Light Source: HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 761.8 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.09
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 11.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P433612

CATALOG NUMBER: LAMR4B108R709030DE010x1MB

Luminous Intensity Polar Plot





TEST NUMBER: P433612

CATALOG NUMBER: LAMR4B108R709030DE010x1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	104		110	107	105	103		103	101	100		100	98	97		96	95	94
2	106	101	96	92		104	99	95	91		96	92	89		93	90	87		90	88	86
3	100	93	87	83		98	91	86	82		89	84	81		86	82	79		84	81	78
4	94	85	79	74		92	84	78	74		82	77	73		80	76	72		78	74	71
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	64	60
7	78	68	61	56		77	67	61	56		66	60	56		65	59	56		63	59	55
8	74	63	57	52		73	63	56	52		62	56	52		60	55	51		59	55	51
9	70	59	52	48		69	59	52	48		58	52	48		57	51	48		56	51	47
10	66	55	49	45		65	55	49	44		54	48	44		53	48	44		52	48	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	276243
5°	271108
10°	274242
15°	282004
20°	282473
25°	256296
30°	228965
35°	201110
40°	148070
45°	82962
50°	40834
55°	22881
60°	13913
65°	9106
70°	6780
75°	5909
80°	4546
85°	4529



TEST NUMBER: P433612

CATALOG NUMBER: LAMR4B108R709030DE010x1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	6.9
10°-20°	155.6	20.4
20°-30°	215.9	28.3
30°-40°	203.1	26.7
40°-50°	97.0	12.7
50°-60°	25.7	3.4
60°-70°	8.1	1.1
70°-80°	3.3	0.4
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.8	55.6
0°-40°	626.9	82.3
0°-60°	749.5	98.4
0°-90°	761.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	560	
5°	547	52
15°	552	156
25°	471	216
35°	334	203
45°	119	97
55°	27	26
65°	8	8
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P433612

CATALOG NUMBER: LAMR4B108R709030DE010x1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	559.9
2.5°	552.9
5°	547.4
7.5°	546.6
10°	547.4
12.5°	549.0
15°	552.1
17.5°	552.1
20°	538.0
22.5°	508.3
25°	470.8
27.5°	433.2
30°	401.9
32.5°	371.5
35°	333.9
37.5°	285.4
40°	229.9
42.5°	171.3
45°	118.9
47.5°	79.0
50°	53.2
52.5°	36.8
55°	26.6
57.5°	18.8
60°	14.1
62.5°	10.2
65°	7.8
67.5°	5.5
70°	4.7
72.5°	3.9
75°	3.1
77.5°	2.3
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)